

# Relays Overview



## Benefit from More Than 35 Years of Experience







[www.wago.com/relays-and-optocouplers](http://www.wago.com/relays-and-optocouplers)

Series	Item Number	Nominal Input Voltage	Limiting Continuous Current	Contact Type		AU				ANSI/ISA					
<b>857 Series (module width: 6 mm)</b>															
	857-359	24 ... 230 VAC/DC	6 A	1 changeover contact											
	857-369														
	857-303	12 VDC													
	857-304	24 VDC													
	857-314														
	857-1330	24 VAC/DC			4 A	2 x 1 make contact									
	857-354														
	857-357	115 VAC/DC													
	857-358	230 VAC/VDC			6 A	1 changeover contact									
	857-358/006-000	230 VAC													
857-368/006-000															
<b>Timer Relays (module width: 6 mm)</b>															
	857-604	24 VDC	6 A	1 changeover contact											
	857-640														
	857-642														
<b>859 Series (module width: 6 mm)</b>															
	859-302	5 VDC	5 A	1 changeover contact											
	859-312														
	859-303	12 VDC													
	859-353	12 VAC/VDC													
	859-390	24 VDC			3 A										
	859-392														
	859-398														
	859-304	24 VAC/DC			5 A										
	859-314														
	859-354	36 VDC			3 A										
	859-386														
	859-394														
	859-397	48 VDC			5 A										
	859-384														
	859-305	48 VAC/DC			5 A										
	859-355	60 VAC/DC													
	859-356	72 VDC													
	859-393	110 VDC			3 A										
	859-399														
	859-391														
	859-317	115 VAC/DC			5 A										
	859-357														
	859-367	115 VAC													
	859-360	220 VDC			5 A										
	859-308														
	859-318														
	859-358	230 VAC/VDC			230 VAC										
	859-368														
859-359															

**WE INNOVATE!**

0888-0192/0001-6901 – RELAIS Z-CARD 1.0 US – 10/2016  
Printed in Germany – Subject to design changes

WAGO is a registered trademark of WAGO Verwaltungsgesellschaft mbH.  
"Copyright – WAGO Kontakttechnik GmbH & Co. KG – All rights reserved. The content and structure of the WAGO websites, catalogs, videos and other WAGO media are subject to copyright. Distribution or modification to the contents of these pages and videos is prohibited. Furthermore, the content may neither be copied nor made available to third parties for commercial purposes. Also subject to copyright are the images and videos that were made available to WAGO Kontakttechnik GmbH & Co. KG by third parties."

Series	Item Number	Nominal Input Voltage	Limiting Continuous Current	Contact Type		AU				ANSI/ISA			
<b>788 Series (module width: 15 mm)</b>													
	788-311	12 VDC	8 A	2 changeover contacts									
	788-303		16 A	1 changeover contact									
	788-353												
	788-906*	24 VDC	0.3 A	2 changeover contacts									
	788-312		8 A										
	788-412		8 A										
	788-346		6 A										
	788-384*		8 A										
	788-390												
	788-356				1 make contact								
	788-357												
	788-304	24 VAC	16 A	1 changeover contact									
	788-404												
	788-391		8 A	2 changeover contacts									
	788-341		16 A	1 changeover contact									
	788-354	48 VDC	8 A	2 changeover contacts									
	788-512		16 A	1 changeover contact									
	788-546												
	788-506	60 VDC	8 A	2 changeover contacts									
	788-541		16 A	1 changeover contact									
	788-313	110 VDC	8 A	2 changeover contacts									
	788-305		16 A	1 changeover contact									
	788-314	115 VAC	8 A	2 changeover contacts									
	788-306		16 A	1 changeover contact									
	788-315												
	788-307	230 VAC	8 A	2 changeover contacts									
	788-515		8 A	2 changeover contacts									
	788-548		16 A	1 changeover contact									
	788-615												
	788-507	230 VAC	8 A	2 changeover contacts									
	788-607		16 A	1 changeover contact									
	788-543												
	788-516	230 VAC	8 A	2 changeover contacts									
	788-616		16 A	1 changeover contact									
	788-549												
	788-508												
	788-608												
	788-544												
<b>858 Series (module width: 31 mm)</b>													
	858-303	24 VDC	5 A	4 changeover contacts									
	858-304												
	858-314												
	858-354												
	858-355	24 VAC	6 A	2 changeover contacts									
	858-390		12 A										
	858-324												
	858-504	48 VDC	5 A	4 changeover contacts									
	858-514												
	858-305	110 VDC	12 A	2 changeover contacts									
	858-325												
	858-307	115 VAC	5 A	4 changeover contacts									
	858-392												
	858-327	220 VDC	6 A	2 changeover contacts									
	858-507												
	858-517												
	858-308	230 VAC	5 A	4 changeover contacts									
	858-391												
	858-328	230 VAC	12 A	2 changeover contacts									
	858-508												
	858-518	230 VAC	5 A	4 changeover contacts									
	858-528												

\*Positively force-guided contacts