



# 得益于35余年的丰富经验

[www.wago.com/relays-and-optocouplers/cn](http://www.wago.com/relays-and-optocouplers/cn)

| 系列                         | 型号              | 额定输入电压            | 最大工作电流 | 触点类型       |  | AU |  |  |  | ANSI/ISA |  |  |  |
|----------------------------|-----------------|-------------------|--------|------------|--|----|--|--|--|----------|--|--|--|
| <b>857系列 (模块宽度 : 6 mm)</b> |                 |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 857-359         | 24 ... 230 VAC/DC | 6 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 857-369         | 12 VDC            |        |            |  |    |  |  |  |          |  |  |  |
|                            | 857-303         | 24 VDC            | 4 A    | 2 x 1个常开触点 |  |    |  |  |  |          |  |  |  |
|                            | 857-304         | 24 VDC            |        |            |  |    |  |  |  |          |  |  |  |
|                            | 857-314         | 24 VDC            |        |            |  |    |  |  |  |          |  |  |  |
|                            | 857-1330        | 24 VAC/DC         | 6 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 857-354         | 115 VAC/DC        |        |            |  |    |  |  |  |          |  |  |  |
|                            | 857-357         | 230 VAC/VDC       | 6 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 857-358         | 230 VAC           |        |            |  |    |  |  |  |          |  |  |  |
|                            | 857-358/006-000 | 230 VAC           |        |            |  |    |  |  |  |          |  |  |  |
|                            | 857-368/006-000 |                   |        |            |  |    |  |  |  |          |  |  |  |
| <b>时间继电器 (模块宽度 : 6 mm)</b> |                 |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 857-604         | 24 VDC            | 6 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 857-640         |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 857-642         |                   |        |            |  |    |  |  |  |          |  |  |  |
| <b>859系列 (模块宽度 : 6 mm)</b> |                 |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 859-302         | 5 VDC             | 5 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 859-312         |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 859-303         | 24 VDC            | 3 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 859-353         |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 859-390         |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 859-392         | 24 VDC            | 5 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 859-398         |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 859-304         |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 859-314         | 24 VAC/DC         | 3 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 859-354         |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 859-386         | 48 VDC            | 5 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 859-394         |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 859-397         | 48 VAC/DC         | 3 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 859-384         |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 859-305         | 60 VAC/DC         | 5 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 859-355         |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 859-356         | 72 VDC            | 3 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 859-393         |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 859-399         | 110 VDC           | 5 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 859-391         |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 859-317         | 115 VAC/DC        | 3 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 859-357         |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 859-367         | 115 VAC           | 5 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 859-360         |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 859-308         | 220 VDC           | 3 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 859-318         |                   |        |            |  |    |  |  |  |          |  |  |  |
|                            | 859-358         | 230 VAC/VDC       | 5 A    | 1个转换触点     |  |    |  |  |  |          |  |  |  |
|                            | 859-368         |                   |        |            |  |    |  |  |  |          |  |  |  |
| 859-359                    | 230 VAC         |                   |        |            |  |    |  |  |  |          |  |  |  |

| 系列                 | 型号       | 额定输入电压  | 最大工作电流 | 触点类型   |        | AU |  |  |  | ANSI/ISA |  |  |  |
|--------------------|----------|---------|--------|--------|--------|----|--|--|--|----------|--|--|--|
| 788系列(模块宽度: 15 mm) |          |         |        |        |        |    |  |  |  |          |  |  |  |
|                    | 788-311  | 12 VDC  | 8 A    | 2个转换触点 |        |    |  |  |  |          |  |  |  |
|                    | 788-303  |         | 16 A   | 1个转换触点 |        |    |  |  |  |          |  |  |  |
|                    | 788-353  |         |        |        |        |    |  |  |  |          |  |  |  |
|                    | 788-906* | 24 VDC  | 0.3 A  | 2个转换触点 |        |    |  |  |  |          |  |  |  |
|                    | 788-312  |         | 8 A    |        |        |    |  |  |  |          |  |  |  |
|                    | 788-412  |         |        |        |        |    |  |  |  |          |  |  |  |
|                    | 788-346  |         |        |        |        |    |  |  |  |          |  |  |  |
|                    | 788-384* |         | 6 A    |        |        |    |  |  |  |          |  |  |  |
|                    | 788-390  |         | 8 A    |        |        |    |  |  |  |          |  |  |  |
|                    | 788-356  |         | 1个常开触点 |        |        |    |  |  |  |          |  |  |  |
|                    | 788-357  |         |        |        |        |    |  |  |  |          |  |  |  |
|                    | 788-304  | 16 A    |        | 1个转换触点 |        |    |  |  |  |          |  |  |  |
|                    | 788-404  |         |        |        |        |    |  |  |  |          |  |  |  |
|                    | 788-391  |         |        |        |        |    |  |  |  |          |  |  |  |
|                    | 788-341  |         |        |        |        |    |  |  |  |          |  |  |  |
|                    | 788-354  | 24 VAC  |        | 2个转换触点 |        |    |  |  |  |          |  |  |  |
|                    | 788-512  |         | 8 A    |        |        |    |  |  |  |          |  |  |  |
|                    | 788-546  |         |        |        |        |    |  |  |  |          |  |  |  |
|                    | 788-506  |         | 16 A   | 1个转换触点 |        |    |  |  |  |          |  |  |  |
|                    | 788-541  | 48 VDC  |        | 2个转换触点 |        |    |  |  |  |          |  |  |  |
|                    | 788-313  |         | 8 A    |        |        |    |  |  |  |          |  |  |  |
|                    | 788-305  |         | 16 A   |        | 1个转换触点 |    |  |  |  |          |  |  |  |
|                    | 788-314  | 60 VDC  | 8 A    | 2个转换触点 |        |    |  |  |  |          |  |  |  |
|                    | 788-306  |         | 16 A   | 1个转换触点 |        |    |  |  |  |          |  |  |  |
|                    | 788-315  | 110 VDC | 8 A    | 2个转换触点 |        |    |  |  |  |          |  |  |  |
|                    | 788-307  |         | 16 A   | 1个转换触点 |        |    |  |  |  |          |  |  |  |
|                    | 788-515  | 115 VAC |        | 2个转换触点 |        |    |  |  |  |          |  |  |  |
|                    | 788-548  |         | 8 A    |        |        |    |  |  |  |          |  |  |  |
|                    | 788-615  |         |        |        | 1个转换触点 |    |  |  |  |          |  |  |  |
|                    | 788-507  |         | 16 A   |        |        |    |  |  |  |          |  |  |  |
|                    | 788-607  | 230 VAC |        | 2个转换触点 |        |    |  |  |  |          |  |  |  |
|                    | 788-543  |         | 8 A    |        |        |    |  |  |  |          |  |  |  |
|                    | 788-516  |         |        |        |        |    |  |  |  |          |  |  |  |
|                    | 788-616  | 16 A    |        | 1个转换触点 |        |    |  |  |  |          |  |  |  |
|                    | 788-549  |         | 8 A    |        |        |    |  |  |  |          |  |  |  |
|                    | 788-508  |         |        |        |        |    |  |  |  |          |  |  |  |
|                    | 788-608  | 230 VAC |        | 2个转换触点 |        |    |  |  |  |          |  |  |  |
|                    | 788-544  |         | 16 A   |        | 1个转换触点 |    |  |  |  |          |  |  |  |

|                    |         |         |      |        |  |  |  |  |  |  |  |  |  |
|--------------------|---------|---------|------|--------|--|--|--|--|--|--|--|--|--|
| 858系列(模块宽度: 31 mm) |         |         |      |        |  |  |  |  |  |  |  |  |  |
|                    | 858-303 | 24 VDC  | 5 A  | 4个转换触点 |  |  |  |  |  |  |  |  |  |
|                    | 858-304 |         |      |        |  |  |  |  |  |  |  |  |  |
|                    | 858-314 |         |      |        |  |  |  |  |  |  |  |  |  |
|                    | 858-354 |         |      |        |  |  |  |  |  |  |  |  |  |
|                    | 858-355 | 12 A    | 6 A  | 2个转换触点 |  |  |  |  |  |  |  |  |  |
|                    | 858-390 |         |      |        |  |  |  |  |  |  |  |  |  |
|                    | 858-324 | 24 VAC  | 5 A  | 4个转换触点 |  |  |  |  |  |  |  |  |  |
|                    | 858-504 |         |      |        |  |  |  |  |  |  |  |  |  |
|                    | 858-514 | 48 VDC  | 12 A | 2个转换触点 |  |  |  |  |  |  |  |  |  |
|                    | 858-305 |         |      |        |  |  |  |  |  |  |  |  |  |
|                    | 858-325 | 110 VDC | 5 A  | 4个转换触点 |  |  |  |  |  |  |  |  |  |
|                    | 858-307 |         |      |        |  |  |  |  |  |  |  |  |  |
|                    | 858-392 | 115 VAC | 6 A  | 2个转换触点 |  |  |  |  |  |  |  |  |  |
|                    | 858-327 |         |      |        |  |  |  |  |  |  |  |  |  |
|                    | 858-507 | 220 VDC | 5 A  | 4个转换触点 |  |  |  |  |  |  |  |  |  |
|                    | 858-517 |         |      |        |  |  |  |  |  |  |  |  |  |
|                    | 858-308 | 230 VAC | 6 A  | 2个转换触点 |  |  |  |  |  |  |  |  |  |
|                    | 858-391 |         |      |        |  |  |  |  |  |  |  |  |  |
|                    | 858-328 | 230 VAC | 5 A  | 4个转换触点 |  |  |  |  |  |  |  |  |  |
|                    | 858-508 |         |      |        |  |  |  |  |  |  |  |  |  |
|                    | 858-518 | 230 VAC | 12 A | 2个转换触点 |  |  |  |  |  |  |  |  |  |
|                    | 858-528 |         |      |        |  |  |  |  |  |  |  |  |  |

\*带有强制触点