

Relays Overview



Benefit from More Than 35 Years of Experience






www.wago.com/relays-and-optocouplers

Series	Item Number	Nominal Input Voltage	Limiting Continuous Current	Contact Type													
857 Series (module width: 6 mm)																	
	857-359	24 ... 230 VAC/DC	6 A	1 changeover contact													
	857-369																
	857-303	12 VDC															
	857-304	24 VDC															
	857-314																
	857-1330	24 VAC/DC			4 A	2 x 1 make contact											
	857-354	115 VAC/DC			6 A	1 changeover contact											
	857-357																
	857-358						230 VAC/VDC										
	857-358/006-000						230 VAC										
	857-368/006-000																
Timer Relays (module width: 6 mm)																	
	857-604	24 VDC	6 A	1 changeover contact													
	857-640																
	857-642																
859 Series (module width: 6 mm)																	
	859-302	5 VDC	5 A	1 changeover contact													
	859-312																
	859-303	12 VDC															
	859-353	12 VAC/VDC															
	859-390	24 VDC			3 A												
	859-392																
	859-398																
	859-304																
	859-314	24 VAC/DC			5 A												
	859-354																
	859-386	36 VDC			3 A												
	859-394																
	859-397																
	859-384					48 VDC											
	859-305	48 VAC/DC			5 A												
	859-355																
	859-356	60 VAC/DC															
	859-393	72 VDC			3 A												
	859-399																
	859-391	110 VDC															
	859-317	115 VAC/DC			5 A												
	859-367					115 VAC											
	859-360	220 VDC			5 A												
	859-308																
	859-318																
	859-358	230 VAC/VDC			230 VAC												
	859-368																
	859-359																

WE INNOVATE!

0888-0192/0001-6901 – RELAIS Z-CARD 1.0 US – 10/2016
Printed in Germany – Subject to design changes

WAGO is a registered trademark of WAGO Verwaltungsgesellschaft mbH.
"Copyright – WAGO Kontakttechnik GmbH & Co. KG – All rights reserved. The content and structure of the WAGO websites, catalogs, videos and other WAGO media are subject to copyright. Distribution or modification to the contents of these pages and videos is prohibited. Furthermore, the content may neither be copied nor made available to third parties for commercial purposes. Also subject to copyright are the images and videos that were made available to WAGO Kontakttechnik GmbH & Co. KG by third parties."

Series	Item Number	Nominal Input Voltage	Limiting Continuous Current	Contact Type		AU				ANSI/ISA					
788 Series (module width: 15 mm)															
	788-311	12 VDC	8 A	2 changeover contacts											
	788-303		16 A	1 changeover contact											
	788-353														
	788-906*	24 VDC	0.3 A	2 changeover contacts											
	788-312		8 A												
	788-412		8 A												
	788-346		6 A												
	788-384*		8 A												
	788-390		8 A												
	788-356		16 A		1 make contact										
	788-357														
	788-304														
	788-404														
	788-391	24 VAC	16 A	1 changeover contact											
	788-341		8 A	2 changeover contacts											
	788-354		16 A	1 changeover contact											
	788-512	48 VDC	8 A	2 changeover contacts											
	788-546		16 A	1 changeover contact											
	788-506		8 A	2 changeover contacts											
	788-541	60 VDC	16 A	1 changeover contact											
	788-313		8 A	2 changeover contacts											
	788-305		16 A	1 changeover contact											
	788-314	110 VDC	8 A	2 changeover contacts											
	788-306		16 A	1 changeover contact											
	788-315		8 A	2 changeover contacts											
	788-307	115 VAC	16 A	1 changeover contact											
	788-515		8 A	2 changeover contacts											
	788-548		8 A	2 changeover contacts											
	788-615		16 A	1 changeover contact											
	788-507		8 A	2 changeover contacts											
	788-607		16 A	1 changeover contact											
	788-543	230 VAC	8 A	2 changeover contacts											
	788-516		16 A	1 changeover contact											
	788-616		8 A	2 changeover contacts											
	788-549		16 A	1 changeover contact											
	788-508		8 A	2 changeover contacts											
	788-608		16 A	1 changeover contact											
	788-544														
858 Series (module width: 31 mm)															
	858-303	12 VDC	5 A	4 changeover contacts											
	858-304														
	858-314														
	858-354	24 VDC	12 A	2 changeover contacts											
	858-355		5 A	4 changeover contacts											
	858-390		6 A	2 changeover contacts											
	858-324	48 VDC	12 A	2 changeover contacts											
	858-504		5 A	4 changeover contacts											
	858-514		12 A	2 changeover contacts											
	858-305	110 VDC	5 A	4 changeover contacts											
	858-325		6 A	2 changeover contacts											
	858-307		12 A	4 changeover contacts											
	858-392	115 VAC	5 A	4 changeover contacts											
	858-327		6 A	2 changeover contacts											
	858-507		12 A	4 changeover contacts											
	858-517	220 VDC	5 A	4 changeover contacts											
	858-308		6 A	2 changeover contacts											
	858-391		12 A	4 changeover contacts											
	858-328	230 VAC	5 A	4 changeover contacts											
	858-508		6 A	2 changeover contacts											
	858-518		12 A	4 changeover contacts											
	858-528														

*Positively force-guided contacts