WAGO 10-Conductor Splicing Connectors with Levers, 221 Series

NEW!



Many Possible Applications

The 221 Series Double-Deck Splicing Connector with Levers is an essential tool for any electrician. It's perfect for wiring distribution boxes, especially in building installations like roller shutter controllers, heating circuit distributors, suspended ceilings, safety systems and lighting groups. A key benefit of this connector is that wiring ten conductors of the same potential no longer requires jumpers, so no conductor connections are wasted. The connector can be wired on-site or pre-wired during planning. The 221 Series Double-Deck Splicing Connector with Levers is perfect for installing distributors, but also works great for wiring inside devices.

WAGO 221 Series Splicing Connectors with Levers, with Ten Connection Points

Pull the Lever Up, Insert a Conductor and Push the Lever Back Down – Done!

Wiring using the 221 Series Splicing Connectors with Levers is that simple. And now the family is expanding! Thanks to its user-friendly design, the new 221 Series Double-Deck Splicing Connector with Levers makes it easy for installers to connect up to ten conductors of the same potential – no tools necessary. It offers the same technical features and certifications as the 2-, 3-, and 5-conductor versions of the 221 Series Splicing Connector with Levers.

The Benefits for You:

- Does not waste any conductor connections, unlike commoning methods
- Compact, double-deck design saves space
- Convenient termination of conductors from 0.14 to 4 mm² and stranded conductors from 0.2 to 4 mm²
- Installation of solid, stranded and fine-stranded conductors
- Time savings for installers and device manufacturers
- Flexible options: on-site wiring as needed or pre-wiring according to plan
- A wide range of accessories for secure installation: mounting carriers for vertical and horizontal mounting on DIN-rails, with or without snap-in mounting feet, and strain relief plates

WAGO Mounting Carrier for 10-Conductor Splicing Connectors, 221 Series

Screw and rivet mounting

Centering pin for horizontal use



221

With and without strain relief



221-509 221-509/002-000

WAGO Mounting Carriers are also available in the following versions:

- 221-509/0000-0006
- 221-509/0000-0053
- 221-509/0002-0006
- 221-509/0002-0053

With and without strain relief

Side-by-side lockin



For 15 mm rail

With and without strain relief

WAGO Mounting Carriers are also available in the following versions:

- 221-539/0000-0006
- 221-539/0000-0053
- 221-539/0002-0006
- 221-539/0002-0053
- 221-539/1000-0000
- 221-539/1002-0000



221-539 221-539-002-000

221-539/1000-000 221-539/1002-000

Also for Ex applications

-519



221-519/002-000

WAGO Mounting Carriers are also available in the following versions:

- 221-519/0000-0006
- 221-519/0000-0053
- 221-519/0002-0006
- 221-519/0002-0053

With snap-in mounting feet

With and without strain relief



221-529

221-529/002-000

WAGO Mounting Carriers are also available in the following versions:

- 221-529/0000-0006
- 221-529/0000-0053
- 221-529/0002-0006
- 221-529/0002-0053

g mechanism



For 35 mm rail

With and without strain relief



221-549

221-549/1000-000



221-549-002-000

221-549/1002-000

Also for Ex applications

WAGO Mounting Carriers are also available in the following versions:

- 221-549/0000-0006
- 221-549/0000-0053
- 221-549/0002-0006
- 221-549/0002-0053
- 221-549/1000-0000
- 221-549/1002-0000

WAGO 10-Conductor Splicing Connectors with Levers, 221 Series

Technical Data

WAGO 221 Series
Same technical specifications as all 221 Series products, up to a conductor cross-section of 4 mm²

0.14 … 4 mm² f-str
0.2 … 4 mm² str, s
450 V / 4 kV / 2
32 A
Ambient temperature:
Max. 85 °C (T85)

Available: May 2025

Item Number
221-420

Item Number
221-430

Item Number
221-490

Use only with
WAGO Mounting Carrier,
221 Series

Item Number	221-420	221-430	221-490
Packaging	SPU*: 15 PU**: 150	SPU: 15 PU: 150	SPU: 15 PU: 150
Blister foil	SPU: 5 PU: 90	SPU: 5 PU: 90	SPU: 5 PU: 90

* Subpackaging unit
** Packaging unit

WAGO GmbH & Co. KG
Postfach 2880 · D-32385 Minden
Hansastrasse 27 · D-32423 Minden
info@wago.com
www.wago.com

Headquarter +49 (0)571/ 887 - 0
Sales +49 (0)571/ 887 - 44 222
Orders +49 (0)571/ 887 - 44 333

WAGO is a registered trademark of WAGO Verwaltungsgesellschaft mbH.
"Copyright – WAGO GmbH & Co. KG – All rights reserved. The content and structure of the WAGO websites, catalogs, videos and other WAGO media are subject to copyright. Distribution or modification of the contents of these pages and videos is prohibited. Furthermore, the content may not be copied or made available to third parties for commercial purposes. Also subject to copyright are the images and videos that were made available to WAGO GmbH & Co. KG by third parties."

MM-512504 – 221 10-CONDUCTOR FLYER 1.0 US - 0888-0110/0101-6901 – 12/2024-00 – Printed in Germany – Subject to changes – WAGO is a registered trademark of WAGO Verwaltungsgesellschaft mbH.