

Antennas



Self-Adhesive Antenna; with 2.5 m cable and SMA straight plug; GSM/UMTS/LTE/Bluetooth®/WLAN; 699-960, 1710-2690 MHz

Item No. 758-961

Technical Data	
Frequency band	699 ... 960 MHz 1710 ... 2690 MHz
Dimensions W x H	117 x 12 mm
Cable length	2.5 m
Cable type	RG174
Gain	2.15 dBi
VSWR	< 1.5
Connector	SMA straight plug



Theft-Proof Antenna; with 1 m cable and SMA straight plug; GSM/UMTS/BT/WLAN; 850/900/1800/1900/2100/2400 MHz

Item No. 758-962

Technical Data	
Frequency band	850 / 900 / 1800 / 1900 / 2100 MHz
Dimensions W x H	29 x 52 mm
Cable length	1 m
Cable type	RG174
Gain	2 dBi
VSWR	< 2
Connector	SMA straight plug



Rod Antenna; with 1 m cable and SMA straight plug; GSM UMTS; 850/900/1800/1900/2100 MHz

Item No. 758-963

Technical Data	
Frequency band	850 / 900 / 1800 / 1900 / 2100 MHz
Dimensions (height)	298 mm
Cable length	1 m
Cable type	RG58
Gain	2.2 dBi
VSWR	< 1.6
Connector	SMA straight plug



Magnetic-Mount Antenna; with 2.5 m cable and SMA straight plug; GSM UMTS; 850/900/1800/1900/2100 MHz

Item No. 758-965

Technical Data	
Frequency band	850 / 900 / 1800 / 1900 / 2100 MHz
Dimensions (height)	88 mm
Cable length	2.5 m
Cable type	RG174
Gain	2.2 dBi
VSWR	< 2
Connector	SMA straight plug



Theft-Proof Combination Antenna; with 2.5 m cable and SMA straight plug; GSM UMTS; 850/900/1800/1900/2100 MHz

Item No. 758-966

Technical Data	
Frequency band	850 / 900 / 1800 / 1900 / 2100 MHz
Dimensions W x H	29 x 52 mm
Cable length	2.5 m
Cable type	RG174
Gain	2 dBi
VSWR	< 2
Connector	SMA straight plug