



Sockets for Miniature Switching Relay and Optocoupler



| | | |
|--|--|--|
| | Sockets for miniature switching relay and optocoupler | |
|--|--|--|



| Description | Item No. | Pack. Unit |
|--|----------------|------------|
| JUMPFLEX® socket for miniature switching relay and optocoupler, AC/DC 24 V for DIN 35 rail | 857-104 | 1 |
| JUMPFLEX® socket for miniature switching relay and optocoupler, AC/DC 110 V for DIN 35 rail | 857-107 | 1 |
| JUMPFLEX® socket for miniature switching relay and optocoupler, AC/DC 230 V for DIN 35 rail | 857-108 | 1 |

Technical Data

Accessories see page 52 + 62 ... 63

| | |
|---------------------------|--|
| Status indication | LED yellow |
| Operating temperature | -25 °C ... +60 °C |
| Storage temperature | -40 °C ... +70 °C |
| Dimensions (mm) W x H x L | 6 x 81 x 94 |
| Wire connection | Height from upper-edge of DIN 35 rail CAGE CLAMP®S |
| Cross sections | solid: 0.08 mm ² ... 2.5 mm ² / AWG 28 ... 12 fine-stranded: 0.34 mm ² ... 2.5 mm ² / AWG 22 ... 12 |
| Stripped lengths | 9 ... 10 mm / 0.37 in |

Assignment Socket / Replacement Relay / Replacement Optocoupler

| | Input Voltage | Item No. | Socket | Replacement Relays or Optocouplers | |
|----------------------------|--|-------------|---------|------------------------------------|---------|
| Miniature Switching Relays | 12 V DC | 857-303 | 857-103 | 857-150 | |
| | 24 V DC | 857-304 | 857-104 | 857-152 | |
| | 48 V DC | 857-305 | 857-105 | 857-154 | |
| | 60 V DC | 857-306 | 857-106 | 857-155 | |
| | 110 V DC | 857-307 | 857-107 | 857-155 | |
| | 220 V DC | 857-308 | 857-108 | 857-155 | |
| | 24 V AC/DC | 857-354 | 857-104 | 857-152 | |
| | 115 V AC/DC | 857-357 | 857-107 | 857-155 | |
| | 230 V AC/DC | 857-358 | 857-108 | 857-155 | |
| | Miniature Switching Relays (gold contacts) | 24 V DC | 857-314 | 857-104 | 857-153 |
| 110 V DC | | 857-317 | 857-107 | 857-157 | |
| 220 V DC | | 857-318 | 857-108 | 857-157 | |
| 24 V AC/DC | | 857-364 | 857-104 | 857-153 | |
| 115 V AC/DC | | 857-367 | 857-107 | 857-157 | |
| 230 V AC/DC | | 857-368 | 857-108 | 857-157 | |
| Solid State Relays | | 24 V DC | 857-704 | 857-104 | 857-164 |
| | | 115 V AC/DC | 857-707 | 857-107 | 857-165 |
| | 230 V AC/DC | 857-708 | 857-108 | 857-165 | |
| | 24 V DC | 857-714 | 857-104 | 857-167 | |
| | 115 V AC/DC | 857-717 | 857-107 | 857-168 | |
| | 230 V AC/DC | 857-718 | 857-108 | 857-168 | |
| | 24 V DC | 857-724 | 857-104 | 857-161 | |
| | 115 V AC/DC | 857-727 | 857-107 | 857-162 | |
| 230 V AC/DC | 857-728 | 857-108 | 857-162 | | |