

DESIGN MEETS TECHNOLOGY

Application Visualization with the **e!** DISPLAY 7300T Web Panel



**WE
INNOVATE!**

WAGO[®]

YOUR MACHINE NEEDS A BUSINESS CARD

e!DISPLAY 7300T Web Panel



EASY TO USE – DIRECTLY ADJUST BRIGHTNESS ON THE DISPLAY

e!DISPLAY is the high-performance HMI display with a resistive touch screen for Web-based visualization. On top of its technically advanced features, the Web Panel offers a sleek, user-focused design. The display has been optimized for the best performance – regardless of application type or system size – thanks to four available screen sizes (4.3" / 5.7" / 7.0" and 10.1").

Usability

Sensors can automatically adjust the brightness of e!DISPLAY based on a room's ambient lighting conditions. Additionally, users can also easily and quickly readjust brightness levels to suit their needs. The display carries front-mounted screen setup buttons for exceptional usability.



ENERGY-SAVING SENSORS ENSURE SAFETY

Sensors

e!DISPLAY features an energy-saving, stand-by function with a screen saver. Integrated sensors conveniently and automatically show the previous visualization as a user approaches the display. Operating conditions are recorded via temperature sensor and can be used for reliable testing. Status LEDs indicate both operating status and operational feedback at all times.

Mounting

e!DISPLAY directly latches onto the control cabinet via mounting clips for quick and easy tool-free installation. Achieve IP65 levels of protection for the front of the display with additional clamping elements. This design flexibility makes e!DISPLAY extremely versatile and suitable for a wide variety of applications. The VESA mount allows universal mounting accessories to be conveniently used outside of the control panel.



**INSTALLED IN A SNAP —
THOUGHTFULLY DESIGNED
FOR MOUNTING FLEXIBILITY**


All from the Same Source





The more harmonious component integration is, the better performance and reliability will be. **e!DISPLAY** provides high-quality visualizations via CODESYS 2 and WAGO's **e!COCKPIT** engineering software (based on CODESYS 3). It also offers users new technologies, such as HTML5. High-performance solutions are yours when **e!DISPLAY** is combined with WAGO's industry-leading PFC200 and PFC100 Controllers.

Please find additional information at www.wago.com/edisplay



**UNMATCHED
PERFORMANCE —
BENEFIT FROM SINGLE-
SOURCE COMPONENTS**



	Size	Item Number
	4.3"	762-3000
	5.7"	762-3001
	7.0"	762-3002
	10.1"	762-3003

**WE
INNOVATE!**



WAGO[®]

WAGO Kontakttechnik GmbH & Co. KG
Postfach 28 80 · D - 32385 Minden
Hansastraße 27 · D - 32423 Minden
Germany
Phone: +49 571 887-0
Fax: +49 571 887-169
Email: info@wago.com
Online: www.wago.com