

2-Channel Analog Output Module 0-10 V/±10V




Fig. Series 750 / Technical data see page 28 / Delivery without Mini WSB marker  
Series 750 / 753 marking see pages 16 ... 17 / 18 ... 19

The analog output module creates a standardized signal of 0-10 V or ±10 V.

The output signal is electrically isolated and will be transmitted with a resolution of 12 bits.

Outputs are short circuit protected.

The internal system supply is used for the power supply of the module.

The output channels have one common ground potential.

Description	Item no.	Pack. unit
2AO 0-10V DC	750-550	10 <sup>1)</sup>
2AO ± 10V DC	750-556	10 <sup>1)</sup>
2AO 0-10V DC/S5 <sup>2)</sup>	750-550/000-200	1
2AO ±10V DC/S5 <sup>2)</sup>	750-556/000-200	1
2AO 0-10V DC (without connector)	753-550	10 <sup>1)</sup>
2AO ±10V DC (without connector)	753-556	10 <sup>1)</sup>
<sup>1)</sup> Also available individually		
<sup>2)</sup> Data format for S5 control with FB 251		
Accessories	Item no.	Pack. unit
753 Series connector	753-110	25
Coding elements	753-150	100
<b>Miniature WSB quick marking system,</b>		
plain	248-501	5
with marking	see pages 256 ... 257	
Approvals		
Series 750 and 753		
Conformity marking	CE	
UL 508		
ANSI/ISA 12.12.01	Class I, Div. 2, Grp. ABCD, T4	
Series 750		
EN 60079-15	I M2 / II 3 GD Ex nA IIC T4	
Marine applications	see "Approvals Overview" in section 1	

Technical Data	
No. of outputs	2
Current consumption (internal)	65 mA
Voltage supply	via system voltage DC/DC
Signal voltage	0 V ... 10 V (750-550, 753-550) ±10 V (750-556, 753-556)
Load impedance	> 5 kΩ
Linearity	±10 mV
Resolution	12 bits
Conversion time	ca. 2 ms
Output filter settle time (typ.)	300 μs
Measuring error (25 °C)	< ± 0.1 % of the full scale value
Temperature coefficient	< ± 0.01 % /K of the full scale value
Isolation	500 V system/supply
Bit width	2 x 16 bits data 2 x 8 bits control/status (option)
Wire connection	CAGE CLAMP®
Cross sections	0.08 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> / AWG 28 ... 14
Stripped lengths (750 / 753 Series)	8 ... 9 mm / 0.33 in 9 ... 10 mm / 0.37 in
Width	12 mm
Weight	50.5 g
EMC CE-Immunity to interference	acc. to EN 50082-2 (1996)
EMC CE-Emission of interference	acc. to EN 50081-1 (1993)
EMC marine applications -	
Immunity to interference	acc. to Germanischer Lloyd (2003)
EMC marine applications -	
Emission of interference	acc. to Germanischer Lloyd (2003)