



Delivered without miniature WSB markers

The 750-655 AS-I Master Module connects AS-Interface systems to a higher-level fieldbus. The module acts as a master for the AS-Interface and as a slave for the fieldbus. The 75x-655 AS-I Master Module is an M4 master per AS-Interface V3.0 Specification. This means:

- Up to 62 AS-Interface slaves can be connected per AS-I line
- Analog signal transfer is integrated in the masters
- Slave profile support complies with V3.0
- Combined 1-5 transaction types and acyclic write/read services are implemented.

The AS-I functions are provided both cyclically and acyclically via the fieldbus. In cyclic data transfer, up to 32 bytes of I/O data are transferred for the AS-I line binary data. Free cyclic process image areas can be mapped with analog values. Furthermore, analog signals and all other commands and data of the new AS-I specification can be transferred in a management channel via the fieldbus.

Diagnostics, which go far beyond the AS-I specifications, simplify the detection of both sporadic configuration errors and AS-I communication interferences. An auto-installation mode allows an AS-Interface network to be created via sequential slave installation, with no addressing tool required. Both signal transmission and operating status, as well as trouble-free internal data bus communication are indicated via LEDs.

Description	Item No.	Pack. Unit
AS-Interface Master M4 V3.0	750-655	1
AS-Interface Master M4 V3.0 (without connector)	753-655	1
Accessories		
753 Series	753-110	25
Coding elements	753-150	100
Miniature WSB Quick marking system		
plain	248-501	5
with marking	see Full Line Catalog 2010/2011	
	Volume 3, Section 1	
Approvals		
750 and 753 Series		
Conformity marking	CE	
AS-Interface certificate	ZU 50601	
UL 508		
ANSI/ISA 12.12.01	Class I, Div. 2, Grp. ABCD, T4	
750 Series		
EN 60079-15	I M2 / II 3 GD Ex nA IIC T4	
Shipbuilding	GL, Polski Rejestr Statkov	

Technical Data	
AS-I specification	3.0
No. of slaves	up to 62
Current consumption (AS-I)	40 mA
Voltage supply (AS-I)	26.5 V ... 31.6 V
Max. length of AS-I cable	100 m (300 m through repeater)
Cycle time AS-I	0.3 ms ... 10 ms, depending on the number of slaves
Configuration	via process image, WAGO-I/O-CHECK
Transmission channel	1
Max. current consumption (internal)	55 mA
Voltage supply	via system voltage DC/DC
Isolation	500 V system/supply/AS-I
Bit width	max. 12 ... 48 bytes, configurable including 1 byte control/status
Wire connection	CAGE CLAMP®
Cross sections	0.08 mm ² ... 2.5 mm ² / AWG 28 ... 14
Stripped lengths, 750/753 Series	8 ... 9 mm / 0.33 in
	9 ... 10 mm / 0.37 in
Width	12 mm
Weight	56 g
EMC: CE - immunity to interference	acc. to EN 61000-6-2 (2005)
EMC: CE - emission of interference	acc. to EN 61000-6-4 (2007)
EMC: marine applications	
- immunity to interference	acc. to Germanischer Lloyd (2003)
EMC: marine applications	
- emission of interference	acc. to Germanischer Lloyd (2003)