


Switched-Mode Power Supply, 1-Phase

EPSITRON® PRO Power



- Primary switch mode power supply unit with PowerBoost and TopBoost
- Stand-by input for switching off the output and minimizing power consumption
- DC OK contact for output monitoring
- Suitable for both parallel and series operation
- Natural convection cooling when horizontally mounted
- Enclosed for use in switchgear cabinets
- Electrically isolated output voltage (SELV) acc. to EN 60950-1/UL 60950-1

Description	Item No.	Pack. Unit
Switched-mode power supply, 12 V DC / 6 A	787-819	1

Technical Data	
Environmental requirements:	
Ambient operating temperature	-25 °C ... +70 °C
Storage temperature	-25 °C ... +85 °C
Rel. humidity	5 % ... 96 % (no condensation permissible)
Derating	-3 % / K (> +50 °C)
Degree of pollution	2 (acc. to EN 50178)
Climatic category	3K3 (acc. to EN 60721)
Safety and protection:	
Test voltage pri.-sec./ pri.-gr. / sec.-gr.	4.2 kV DC / 2.2 kV DC / 0.7 kV DC
Protection class	I
Degree of protection	IP20 (acc. to EN 60529)
Overvoltage category	II
Overvoltage protection	Via varistor at primary circuit
Short circuit protection	Yes
No-load proof	Yes
Feedback voltage	Max. 25 VDC
Parallel operation	Yes
Series connection	Yes
MTBF	> 500000 h (acc. to IEC 61709)
Connection and type of mounting:	
Wire connection	Input/Output: WAGO 231 Series Signalising: WAGO 733 Series
Cross sections	Input/Output: 0.08 mm ² ... 2.5 mm ² / 28 ... 12 AWG Signalising: 0.08 mm ² ... 0.5 mm ² / 28 ... 20 AWG
Strip lengths	Input/Output: 8 ... 9 mm / 0.31 ... 0.35 in. Signalising: 5 ... 6 mm / 0.2 ... 0.24 in.
Type of mounting	DIN-rail mounting (EN 60715) in 2 positions
Dimensions and weight:	
Dimensions (mm) W x H x L	40 x 163 x 163 (incl. female connector) Length from upper-edge of DIN 35 rail
Weight	800 g
Standards and approvals:	
Standards/specifications	EN 60950, EN 61204-3, UL 60950, EN 61558-2-16, UL 508

Technical Data	
Input:	
Nominal input voltage $V_{i, nom}$	110 ... 240 VAC
Input voltage range	85 ... 264 VAC; 120 ... 350 VDC
Input voltage derating	-5 % / V AC < 95 VAC
Frequency	50 Hz ... 60 Hz
Input current I_i	0.51 A at 230 VAC and 6 ADC
Discharge current	1 mA typ.
Inrush current	< 30 A (peak)
Mains failure hold-up time	70 ms typ. at 230 VAC
Output:	
Nominal output voltage $V_{o, nom}$	12 VDC (SELV)
Output voltage range	11 ... 18 VDC adjustable
Output current I_o	6 A at 12 V DC
PowerBoost	12 ADC (for 4 s); 9 ADC (for 8 s)
TopBoost	21 ADC (for 25 ms)
Factory preset	12 VDC
Adjustment accuracy	1%
Residual ripple	< 70 mV (peak-to-peak)
Current limitation	1.1 x I_o typ.
Overload behavior	TopBoost / PowerBoost / Constant current
Operational indication	LED green (DC OK), LED red (error)
Signaling	Relay contact DC OK (changeover contact)
Efficiency / power losses:	
Efficiency	83 % typ.
Power loss P_V	0.5 W (stand-by) / 3.0 W (no load) / 9.4 W (rated load)
Fuse protection:	
Internal fuse	T 2 A / 250 V
External fuse	Circuit breakers 6 A, 10 A, 16 A, B or C characteristic; an external DC fuse is required for the DC input voltage