

# Analog Signal Conditioning Module in DIN-Rail-mountable Enclosure


1/1

Input signal  $\pm 10$  V

Data sheet



Similar illustration



Description	Item-No.	Pack.-unit pcs																																							
Measuring output $\pm 10$ V	787-365	1																																							
<ul style="list-style-type: none"> <li>Analog signal conditioning module for signal transformation, amplification and transmission with electrical isolation of input and output of standard signals.</li> <li>Electrical isolated supply of input and output via DC/DC-converter.</li> <li>Module in DIN-rail mountable enclosure.</li> <li>Multi connection system. (WAGO series 734)</li> </ul>	<b>Technical Data</b>																																								
	<p><b>Measuring input:</b></p> <table> <tr><td>Input signal</td><td><math>\pm 10</math> V</td></tr> <tr><td>Max. input voltage</td><td><math>\pm 13</math> V</td></tr> <tr><td>Input resistance</td><td>100 k<math>\Omega</math></td></tr> </table> <p><b>Measuring output:</b></p> <table> <tr><td>Output signal</td><td><math>\pm 10</math> V</td></tr> <tr><td>Working resistance</td><td><math>\geq 2</math> k<math>\Omega</math></td></tr> </table> <p><b>Transmission characteristics:</b></p> <table> <tr><td>Transmission error (measuring range)</td><td><math>\leq 0.1</math> %</td></tr> <tr><td>Temperature coefficient (full scale)</td><td><math>\leq 0.02</math> % / K</td></tr> <tr><td>Critical frequency (Sinus)</td><td>1 kHz</td></tr> <tr><td>Isolation voltage input/output</td><td>4 kV, 50 Hz, 1 min</td></tr> <tr><td>input/output/auxiliary</td><td>1 kV, 50 Hz, 1 min</td></tr> </table> <p><b>General data:</b></p> <table> <tr><td>Supply voltage RR <math>\leq 6</math> %</td><td></td></tr> <tr><td>input/output</td><td>DC 20-30 V</td></tr> <tr><td>Current consumption input/output</td><td>80 mA</td></tr> <tr><td>Nominal voltage acc. to VDE 0110/ 1.89</td><td>250 V / 4 kV / 3</td></tr> <tr><td>Ambient operating temperature</td><td>0 °C...+55 °C</td></tr> <tr><td>Storage temperature</td><td>-40 °C...+80 °C</td></tr> <tr><td>Dimensions (WxHxD)</td><td>(22,5x105* x74)mm (0.89x4.13* x2.91)in * from upper edge of DIN 35 rail</td></tr> <tr><td>Wire connection</td><td>Plugg. connector with CAGE CLAMP® (WAGO series 734) 0,08-1,5 mm<sup>2</sup> / AWG 28-16</td></tr> <tr><td>Stripped length</td><td>7 mm / 0.28 in</td></tr> <tr><td>EMC-test IEC 801-2/4/5</td><td>Grade B met acc.to EN50082 P.2 (3.94)</td></tr> </table>		Input signal	$\pm 10$ V	Max. input voltage	$\pm 13$ V	Input resistance	100 k $\Omega$	Output signal	$\pm 10$ V	Working resistance	$\geq 2$ k $\Omega$	Transmission error (measuring range)	$\leq 0.1$ %	Temperature coefficient (full scale)	$\leq 0.02$ % / K	Critical frequency (Sinus)	1 kHz	Isolation voltage input/output	4 kV, 50 Hz, 1 min	input/output/auxiliary	1 kV, 50 Hz, 1 min	Supply voltage RR $\leq 6$ %		input/output	DC 20-30 V	Current consumption input/output	80 mA	Nominal voltage acc. to VDE 0110/ 1.89	250 V / 4 kV / 3	Ambient operating temperature	0 °C...+55 °C	Storage temperature	-40 °C...+80 °C	Dimensions (WxHxD)	(22,5x105* x74)mm (0.89x4.13* x2.91)in * from upper edge of DIN 35 rail	Wire connection	Plugg. connector with CAGE CLAMP® (WAGO series 734) 0,08-1,5 mm <sup>2</sup> / AWG 28-16	Stripped length	7 mm / 0.28 in	EMC-test IEC 801-2/4/5
Input signal	$\pm 10$ V																																								
Max. input voltage	$\pm 13$ V																																								
Input resistance	100 k $\Omega$																																								
Output signal	$\pm 10$ V																																								
Working resistance	$\geq 2$ k $\Omega$																																								
Transmission error (measuring range)	$\leq 0.1$ %																																								
Temperature coefficient (full scale)	$\leq 0.02$ % / K																																								
Critical frequency (Sinus)	1 kHz																																								
Isolation voltage input/output	4 kV, 50 Hz, 1 min																																								
input/output/auxiliary	1 kV, 50 Hz, 1 min																																								
Supply voltage RR $\leq 6$ %																																									
input/output	DC 20-30 V																																								
Current consumption input/output	80 mA																																								
Nominal voltage acc. to VDE 0110/ 1.89	250 V / 4 kV / 3																																								
Ambient operating temperature	0 °C...+55 °C																																								
Storage temperature	-40 °C...+80 °C																																								
Dimensions (WxHxD)	(22,5x105* x74)mm (0.89x4.13* x2.91)in * from upper edge of DIN 35 rail																																								
Wire connection	Plugg. connector with CAGE CLAMP® (WAGO series 734) 0,08-1,5 mm <sup>2</sup> / AWG 28-16																																								
Stripped length	7 mm / 0.28 in																																								
EMC-test IEC 801-2/4/5	Grade B met acc.to EN50082 P.2 (3.94)																																								