

Analog Signal Conditioning Module in DIN-Rail-mountable Enclosure


1/1

Input signal ± 10 V

Data sheet



Similar illustration



Description	Item-No.	Pack.-unit pcs																																																		
Measuring output ± 10 mA	787-372	1																																																		
<ul style="list-style-type: none"> • Analog signal conditioning module for signal transformation, amplification and transmission with electrical isolation of input and output of standard signals. • Electrical isolated supply of input and output via DC/DC-converter. • Module in DIN-rail mountable enclosure. • Multi connection system. (WAGO series 734) 	<p>Technical Data</p> <p>Measuring input:</p> <table border="1"> <tr><td>Input signal</td><td>± 10 V</td></tr> <tr><td>Max. input voltage</td><td>± 13 V</td></tr> <tr><td>Input resistance</td><td>> 100 kΩ</td></tr> </table> <p>Measuring output:</p> <table border="1"> <tr><td>Output signal</td><td>± 10 mA</td></tr> <tr><td>Working resistance</td><td>≤ 500 Ω</td></tr> </table> <p>Transmission characteristics:</p> <table border="1"> <tr><td>Transmission error (measuring range)</td><td>≤ 0.1 %</td></tr> <tr><td>Offset error (measuring range)</td><td>≤ 0.1 %</td></tr> <tr><td>Temperature coefficient (full scale)</td><td>≤ 0.02 % / K</td></tr> <tr><td>Critical frequency (Sinus)</td><td>1 kHz</td></tr> </table> <p>Isolation voltage</p> <table border="1"> <tr><td>input/output</td><td>4 kV, 50 Hz, 1 min</td></tr> <tr><td>input/output/auxiliary</td><td>1 kV, 50 Hz, 1 min</td></tr> </table> <p>General data:</p> <table border="1"> <tr><td>Supply voltage RR ≤ 6 %</td><td></td></tr> <tr><td>input/output</td><td>DC 20-30 V</td></tr> <tr><td>Current consumption</td><td></td></tr> <tr><td>input/output</td><td>80 mA</td></tr> <tr><td>Nominal voltage</td><td></td></tr> <tr><td>acc. to VDE 0110/ 1.89</td><td>250 V / 4 kV / 3</td></tr> <tr><td>Ambient operating temperature</td><td>0 °C...+55 °C</td></tr> <tr><td>Storage temperature</td><td>-40 °C...+80 °C</td></tr> <tr><td>Dimensions (WxHxD)</td><td>(22,5x105* x74)mm (0.89x4.13* x2.91)in</td></tr> <tr><td></td><td>* from upper edge of DIN 35 rail</td></tr> <tr><td>Wire connection</td><td>Plugg. connector with CAGE CLAMP® (WAGO series 734)</td></tr> <tr><td></td><td>0,08-1,5 mm² / AWG 28-16</td></tr> <tr><td>Stripped length</td><td>7 mm / 0.28 in</td></tr> <tr><td>EMC-test IEC 801-2/4/5</td><td>Grade B met acc.to EN50082 P.2 (3.94)</td></tr> </table>		Input signal	± 10 V	Max. input voltage	± 13 V	Input resistance	> 100 k Ω	Output signal	± 10 mA	Working resistance	≤ 500 Ω	Transmission error (measuring range)	≤ 0.1 %	Offset error (measuring range)	≤ 0.1 %	Temperature coefficient (full scale)	≤ 0.02 % / K	Critical frequency (Sinus)	1 kHz	input/output	4 kV, 50 Hz, 1 min	input/output/auxiliary	1 kV, 50 Hz, 1 min	Supply voltage RR ≤ 6 %		input/output	DC 20-30 V	Current consumption		input/output	80 mA	Nominal voltage		acc. to VDE 0110/ 1.89	250 V / 4 kV / 3	Ambient operating temperature	0 °C...+55 °C	Storage temperature	-40 °C...+80 °C	Dimensions (WxHxD)	(22,5x105* x74)mm (0.89x4.13* x2.91)in		* from upper edge of DIN 35 rail	Wire connection	Plugg. connector with CAGE CLAMP® (WAGO series 734)		0,08-1,5 mm ² / AWG 28-16	Stripped length	7 mm / 0.28 in	EMC-test IEC 801-2/4/5	Grade B met acc.to EN50082 P.2 (3.94)
Input signal	± 10 V																																																			
Max. input voltage	± 13 V																																																			
Input resistance	> 100 k Ω																																																			
Output signal	± 10 mA																																																			
Working resistance	≤ 500 Ω																																																			
Transmission error (measuring range)	≤ 0.1 %																																																			
Offset error (measuring range)	≤ 0.1 %																																																			
Temperature coefficient (full scale)	≤ 0.02 % / K																																																			
Critical frequency (Sinus)	1 kHz																																																			
input/output	4 kV, 50 Hz, 1 min																																																			
input/output/auxiliary	1 kV, 50 Hz, 1 min																																																			
Supply voltage RR ≤ 6 %																																																				
input/output	DC 20-30 V																																																			
Current consumption																																																				
input/output	80 mA																																																			
Nominal voltage																																																				
acc. to VDE 0110/ 1.89	250 V / 4 kV / 3																																																			
Ambient operating temperature	0 °C...+55 °C																																																			
Storage temperature	-40 °C...+80 °C																																																			
Dimensions (WxHxD)	(22,5x105* x74)mm (0.89x4.13* x2.91)in																																																			
	* from upper edge of DIN 35 rail																																																			
Wire connection	Plugg. connector with CAGE CLAMP® (WAGO series 734)																																																			
	0,08-1,5 mm ² / AWG 28-16																																																			
Stripped length	7 mm / 0.28 in																																																			
EMC-test IEC 801-2/4/5	Grade B met acc.to EN50082 P.2 (3.94)																																																			