

# WAGO TOPJOB® S轨装式接线端子

依托可靠的直插型笼式弹簧连接技术

— 优选 —

系列	2000	2001	2002	2004	2006	2010	2016	
接线范围	0.14 ... 1 (1.5) mm² (24 ... 16 AWG)	0.25 ... 1.5 (2.5) mm² (22 ... 14 AWG)	0.25 ... 2.5 (4) mm² (22 ... 12 AWG)	0.5 ... 4 (6) mm² (20 ... 10 AWG)	0.5 ... 6 (10) mm² (20 ... 8 AWG)	0.5 ... 10 (16) mm² (20 ... 6 AWG)	0.5 ... 16 (25 "f-st") mm² (20 ... 4 AWG)	
额定电压	800 V	800 V	800 V	800 V	800 V	800 V	800 V	
额定电流/(最大电流)	13.5 A (18 A)	18 A (24 A)	24 A (32 A)	32 A (41 A)	41 A (57 A)	57 A (76 A)	76 A (90 A)	
端子厚度	3.5 mm (0.138 inch)	4.2 mm (0.165 inch)	5.2 mm (0.205 inch)	6.2 mm (0.244 inch)	7.5 mm (0.295 inch)	10 mm (0.394 inch)	12 mm (0.472 inch)	
颜色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色
每包数量	100	100	100	50	50	25	20	

系列	2200	2201	2202	2204	2206	2210	2216	
接线范围	0.14 ... 1 (1.5) mm² (24 ... 16 AWG)	0.25 ... 1.5 (2.5) mm² (22 ... 14 AWG)	0.25 ... 2.5 (4) mm² (22 ... 12 AWG)	0.5 ... 4 (6) mm² (20 ... 10 AWG)	0.5 ... 6 (10) mm² (20 ... 8 AWG)	0.5 ... 10 (16) mm² (20 ... 6 AWG)	0.5 ... 16 (25 "f-st") mm² (20 ... 4 AWG)	
额定电压	800 V	800 V	800 V	800 V	800 V	800 V	800 V	
额定电流/(最大电流)	13.5 A (18 A)	18 A (24 A)	24 A (32 A)	32 A (41 A)	41 A (57 A)	57 A (76 A)	76 A (90 A)	
端子厚度	3.5 mm (0.138 inch)	4.2 mm (0.165 inch)	5.2 mm (0.205 inch)	6.2 mm (0.244 inch)	7.5 mm (0.295 inch)	10 mm (0.394 inch)	12 mm (0.472 inch)	
颜色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色
每包数量	100	100	100	50	50	25	20	

系列	2102	2106	2116
接线范围	0.25 ... 2.5 (4) mm² (22 ... 12 AWG)	0.5 ... 6 (10) mm² (20 ... 8 AWG)	0.5 ... 16 (25 "f-st") mm² (20 ... 4 AWG)
额定电压	800 V	800 V	800 V
额定电流/(最大电流)	24 A (30 A)	41 A (55 A)	76 A (90 A)
端子厚度	5.2 mm (0.205 inch)	7.5 mm (0.295 inch)	12 mm (0.472 inch)
颜色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色	灰色 蓝色 黄色 黄绿色
每包数量	50	25	20

系列	2000	2001	2002	2004	2006	2010	2016
模块化插接式连接器, 可组成排, 用于跨接器插孔, 灰色	2000-511	2001-511	2002-511	2004-511	2006-511	2010-511	2016-511
插脚跨接器, 绝缘, 浅灰色	2000-402	2001-402	2002-402	2004-402	2006-402	2010-402	2016-402
板状跨接器, 绝缘, 浅灰色	2000-433	2001-433	2002-433	2004-433	2006-433	2010-433	2016-433
高低跨接器, 绝缘, 浅灰色	2000-499	2001-499	2002-499	2004-499	2006-499	2010-499	2016-499
交错跨接器, 绝缘, 浅灰色	2002-472	2002-473	2002-474	2002-475	2002-476	2002-477	2002-478
预置型交错跨接器, 绝缘, 浅灰色	2002-473/011-000	2002-475/011-000	2002-477/011-000	2002-479/011-000	2002-481/011-000	2002-483/011-000	2002-485/011-000
适用于连续跨接的相邻跨接器, 绝缘, 浅灰色	2002-400						
适用于连续跨接的相邻跨接器, 绝缘, 浅灰色, 蓝色, 红色	2002-423						
导线型跨接器, 绝缘, 灰色, 黑色	2009-402	2009-412	2009-412	2009-412	2009-412	2009-412	2009-412
绝缘止动件, 5个装, 浅灰色, 深灰色	2001-171	2002-171	2002-171	2004-171	2004-171	2004-171	2004-171

## 附件

附件	型号	每包数量
WMB标记系列, 空白		
每板10条, 每条10个标记, 标记牌宽度: 5 ... 5.2 mm (随于2002 ... 2016系列)		
空白标记牌	793-5501	5
标记牌, 水平标记	793-5502	5
1 ... 10	793-5503	5
11 ... 20	793-5504	5
21 ... 30	793-5505	5
31 ... 40	793-5506	5
1 ... 50	793-5507	5
标记牌, 垂直标记	793-5602	5
1 ... 10	793-5603	5
11 ... 20	793-5604	5
21 ... 30	793-5605	5
31 ... 40	793-5606	5
41 ... 50	793-5607	5
51 ... 60	793-5608	5
1 ... 50	793-5609	5
标记牌宽度: 4 ... 4.2 mm (2001系列)		
水平	793-45xx	
标记牌宽度: 3.5 mm (2000系列)		
水平	793-35xx	
WMB卷装标记牌, 空白, 白色		
5 ... 5.2 mm	2009-115	每卷 1500个
4 ... 4.2 mm	2009-114	每卷 2000个
3.5 mm	2009-113	每卷 2300个
标记卷, 卷装, 空白, 白色		
宽度11 mm	2009-110	每卷50m
可调节高度的标记牌支架		
适于标记卷或标记牌	2009-163	50 (2 x 25)
热转印打印机 smartPRINTER		
300 dpi	258-5000	1
打印宽度: 47 mm		
切割器	258-5030	1
热转印墨带	258-5005	1
测试插头适配器		
适于0.4 mm测试插头	2009-174	100 (4 x 25)
可连接最大2.5 mm²导线	2009-182	100 (4 x 25)
终端挡块, 适于DIN 35型导轨		
厚度6 mm	249-116	100 (4 x 25)
厚度10 mm	249-117	50 (2 x 25)
钢制导轨, 35 x 7.5 mm, 长度2 m		
不带孔	210-113	10
带孔	210-112	10
螺丝刀, 带有绝缘手柄		
(2.5 x 0.4) mm	210-719	1
(3.5 x 0.5) mm	210-720	1
(5.5 x 0.8) mm	210-721	1
套装(所有3种型号)	210-722	1
压线钳		
Variocrimp 4压线钳	206-204	1
Variocrimp 16压线钳	206-216	1
剥线钳		
"Quickstrip 10"剥线钳	206-124	1
"Quickstrip 16"剥线钳	206-125	1
不带绝缘护套的冷压接头, 12 mm剥线长度		
0.5 mm²	216-241	1000
0.75 mm²	216-242	1000
1.00 mm²	216-243	1000
1.5 mm²	216-244	1000
还有其他导线截面积及剥线长度可供选择。		



获取更多信息请访问：  
[www.wago.com/topjob-s](http://www.wago.com/topjob-s)

操作孔

推压键

操作杆

附件

相关技术规格及轨装式接线端子的全部信息请参阅总目录第1册。

# WAGO RAIL-MOUNT TERMINAL BLOCKS TOPJOB® S

With Push-in CAGE CLAMP® Reliability

- Excerpt -

Series	2000	2001	2002	2004	2006	2010	2016
Conductor range	0.14 ... 1 (1.5) mm² (24 ... 16 AWG)	0.25 ... 1.5 (2.5) mm² (22 ... 14 AWG)	0.25 ... 2.5 (4) mm² (22 ... 12 AWG)	0.5 ... 4 (6) mm² (20 ... 10 AWG)	0.5 ... 6 (10) mm² (20 ... 8 AWG)	0.5 ... 10 (16) mm² (20 ... 6 AWG)	0.5 ... 16 (25 "f-st") mm² (20 ... 4 AWG)
Rated voltage	800 V	800 V	800 V	800 V	800 V	800 V	800 V
Rated current/(max. current)	13.5 A (18 A)	18 A (24 A)	24 A (32 A)	32 A (41 A)	41 A (57 A)	57 A (76 A)	76 A (90 A)
Terminal block width	3.5 mm (0.138 inch)	4.2 mm (0.165 inch)	5.2 mm (0.205 inch)	6.2 mm (0.244 inch)	7.5 mm (0.295 inch)	10 mm (0.394 inch)	12 mm (0.472 inch)
	Color	Item No.	Packaging Unit	Item No.	Packaging Unit	Item No.	Packaging Unit
2-conductor through/ground terminal block	gray	2000-1201	100	2001-1201	100	2002-1201	100
	blue	2000-1204	100	2001-1204	100	2002-1204	100
	orange	2000-1202	100	2001-1202	100	2002-1202	100
	green-yellow	2000-1207	100	2001-1207	100	2002-1207	100
	End and intermediate plate	orange	2000-1292	100 (4 x 25)	2002-1292	100 (4 x 25)	2002-1292

Series	2200	2201	2202	2204	2206	2210	2216
Conductor range	0.14 ... 1 (1.5) mm² (24 ... 16 AWG)	0.25 ... 1.5 (2.5) mm² (22 ... 14 AWG)	0.25 ... 2.5 (4) mm² (22 ... 12 AWG)	0.5 ... 4 (6) mm² (20 ... 10 AWG)	0.5 ... 6 (10) mm² (20 ... 8 AWG)	0.5 ... 10 (16) mm² (20 ... 6 AWG)	0.5 ... 16 (25 "f-st") mm² (20 ... 4 AWG)
Rated voltage	800 V	800 V	800 V	800 V	800 V	800 V	800 V
Rated current/(max. current)	13.5 A (18 A)	18 A (24 A)	24 A (32 A)	32 A (41 A)	41 A (57 A)	57 A (76 A)	76 A (90 A)
Terminal block width	3.5 mm (0.138 inch)	4.2 mm (0.165 inch)	5.2 mm (0.205 inch)	6.2 mm (0.244 inch)	7.5 mm (0.295 inch)	10 mm (0.394 inch)	12 mm (0.472 inch)
	Color	Item No.	Packaging Unit	Item No.	Packaging Unit	Item No.	Packaging Unit
2-conductor through/ground terminal block, with push-buttons	gray	2200-1201	100	2201-1201	100	2202-1201	100
	blue	2200-1204	100	2201-1204	100	2202-1204	100
	orange	2200-1202	100	2201-1202	100	2202-1202	100
	green-yellow	2200-1207	100	2201-1207	100	2202-1207	100
	End and intermediate plate	orange	2000-1292	100 (4 x 25)	2002-1292	100 (4 x 25)	2002-1292

Series	2102	2106	2116				
Conductor range	0.25 ... 2.5 (4) mm² (22 ... 12 AWG)	0.5 ... 6 (10) mm² (20 ... 8 AWG)	0.5 ... 16 (25 "f-st") mm² (20 ... 4 AWG)				
Rated voltage	800 V	800 V	800 V				
Rated current/(max. current)	24 A (30 A)	41 A (55 A)	76 A (90 A)				
Terminal block width	5.2 mm (0.205 inch)	7.5 mm (0.295 inch)	12 mm (0.472 inch)				
	Color	Item No.	Packaging Unit				
2-conductor through/ground terminal block, with a lever and operating slots	gray	2102-1201	50	2106-1201	25	2116-1201	20
	blue	2102-1204	50	2106-1204	25	2116-1204	20
	orange	2102-1202	50	2106-1202	25	2116-1202	20
	green-yellow	2102-1207	50	2106-1207	25	2116-1207	20
	End and intermediate plate	orange	2102-1292	100 (4 x 25)	2106-1292	100 (4 x 25)	2116-1292

Series	2000	2001	2002	2004	2006	2010	2016
Modular connector for jumper contact slot and spacer module, snaps together, gray	Item No.	Packaging Unit	Item No.	Packaging Unit	Item No.	Packaging Unit	Packaging Unit
Modular connector	2000-511	100 (4x25)	2001-511	100 (4x25)	2002-511	100 (4x25)	2004-511
Spacer module	2000-549	100 (4x25)	2001-549	100 (4x25)	2002-549	100 (4x25)	2004-549
Push-in type jumper bar, insulated, light gray	2-way	2000-402	25	2001-402	25	2002-402	25
	3-way	2000-403	25	2001-403	25	2002-403	25
	4-way	2000-404	25	2001-404	25	2002-404	25
	10-way	2000-410	25	2001-410	25	2002-410	25
	End and intermediate plate	orange	2000-1292	100 (4 x 25)	2002-1292	100 (4 x 25)	2002-1292

OPERATING SLOTS


PUSH-BUTTONS

LEVER

ACCESSORIES

## Accessories

	Item No.	Packaging Unit
WMB Multi marking system, white		
10 strips with 10 markers for terminal blocks		
Marker width: 5 ... 5.2 mm (for 2002 ... 2016 Series)		
Plain marker card	793-5501	5
Printed marker card, horizontal marking		
1 ... 10	793-5502	5
11 ... 20	793-5503	5
21 ... 30	793-5504	5
31 ... 40	793-5505	5
1 ... 50	793-5566	5
Printed marker card, vertical marking		
1 ... 10	793-5602	5
11 ... 20	793-5603	5
21 ... 30	793-5604	5
31 ... 40	793-5605	5
41 ... 50	793-5606	5
51 ... 60	794-5601	5
1 ... 50	793-5666	5
Marker width: 4 ... 4.2 mm (2001 Series)		
horizontal	793-45xx	
Marker width: 3.5 mm (2000 Series)		
horizontal	793-35xx	
WMB inline markers, on reel, plain, white		
5 ... 5.2 mm	2009-115	1 reel (1,500 pcs)
4 ... 4.2 mm	2009-114	1 reel (2,000 pcs)
3.5 mm	2009-113	1 reel (2,300 pcs)
Marking strip, on reel, plain, white		
11 mm wide	2009-110	1 reel (50 m)
Height-adjustable group marker carrier		
for marking strips or markers		
	2009-163	50 (2 x 25)
Thermal Transfer smartPRINTER		
300 dpi	258-5000	1
Print width: 47 mm		
Cutter	258-5030	1
Thermal transfer ink ribbon	258-5005	1
Test plug adapter		
for 4 mm Ø test plug		
	2009-174	100 (4 x 25)
for max. 2.5 mm²		
	2009-182	100 (4 x 25)
Screwless end stop, for DIN-35 rail		
6 mm wide	249-116	100 (4 x 25)
10 mm wide	249-117	50 (2 x 25)
Steel carrier rail, 35 x 7.5 mm, 2 m long		
unslotted	210-113	10
slotted	210-112	10
Operating tool, with a partially insulated shaft		
(2.5 x 0.4) mm	210-719	1
(3.5 x 0.5) mm	210-720	1
(5.5 x 0.8) mm	210-721	1
Set (all 3 sizes)	210-722	1
Crimping tool		
"Variocrimp 4"	206-204	1
"Variocrimp 16"	206-216	1
Stripping tool		
"Quickstrip 10"	206-124	1
"Quickstrip 16"	206-125	1
Insulated ferrule, 12 mm strip length		
0.5 mm²	216-241	1000
0.75 mm²	216-242	1000
1.00 mm²	216-243	1000
1.5 mm²	216-244	1000
Other cross-sections and strip lengths are available.		



Additional information is available at:  
[www.wago.com/topjob-s](http://www.wago.com/topjob-s)

Both technical specifications and all rail-mount terminal blocks can be found in our Full Line Catalog, Volume 1.