Data Sheet - Visual Panel 207

8002-0099/0000-0641

Technical Data	
LCD Size	7" (18 cm) Wide TFT Color
Colors	16.7M Colors
CPU	i.MX8MPlus Quad 1.6GHz
Architecture	ARMv8-A
Luminance	1,000 cd/m²
Viewing Angle	LRUD - 80° Left / 80° Right / 80° Up / 80° Down
Backlight Life	>50,000 Hours
Contrast Ratio	1000 : 1
Touch Panel	4 Wire Resistive
Resolution	1024 x 600 WSVGA (128:75)
Effective Display Area	154.21 (H) x 85.92 (V) mm
Touch Panel Accuracy	Active Area Length (X) ±2%, Width (Y) ±2%
Memory	2 GB LPDDR4
Storage	8 GB eMMC
SD Card Slot	µSD
Ethernet	10/100/1000 2 Ports
COM1	RS-422/485 (5-Pin TB)
COM2	RS-232C (DB9/DSUB 9 Pin)
USB Host	USB 2.0 Type A
Tool Port	USB Type C
Bezel Enclosure	Front & Rear: Plastic
Weight	510 g
Rated Voltage	DC24V (Class 2)
Inrush Current	30 A maximum
Power Use	12W (Max 14 W)
Operating System	Embedded Linux
Audio Port	Line Out
Project Memory	250 MB
User Memory	4 GB
Real-Time Clock	Built-In

Data Sheet - Visual Panel 207

8002-0099/0000-0641

Electronic buzzer	Built-In
Dimension	185 x 127 x 51.9 mm (7.3" x 5" x 2")
Panel Cut	177 x 119 mm (7" x 4.7")
Operating Temp.	-20 °C to 70 °C
Storage Temp.	-25 °C to 75 °C
Operating Humidity	10–90% RH (Below 29°C, Not Condensed)
Storage Humidity	10–90% RH (Below 39 °C, Not Condensed)
Environment Condition	800 hPa–1114 hPa (2000 m/6,500 ft or Less)
Dust	≤ 0.1mg/m^3 (No Conductive Dust Allowed)
Pollution Degree	≤ Pollution Degree 2
Corrosion Immunity	No Corrosive Gas or Dust
Noise Protection	Impulse, EFT/Burst, Surge, ±2 kV, 1 µs
Electrostatic Discharge	4 kV (Contact Discharge), 8 kV (Air Discharge) (IEC 61000-4-2)
Shock Protection	JIS B 3502, IEC/EN 61131-2 Compliant 147 m/s², X, Y, Z Directions ±3 Times (Total 18 Times)
Vibration Protection	JIS B 3502, IEC/EN 61131-2 Compliant 5–9 Hz Single Amplitude: 3.5 mm 9–150 Hz Fixed Acceleration: 9.8 m/s² X, Y, Z Directions for 10 Cycles (Approx. 100 Min)
WAGO Visual Designer	MQTT (SparkPlug), OPC UA, EtherNet/IP, Modbus, Multiple PLC Drivers; Landscape or Portrait Mode
Approvals	CE - UL [cUL] - UKCA
Protection Class	IP68 (front); NEMA 4x, 12 (Front)

WAGO Corporation
N120 W19129 Freistadt Road
Germantown, Wisconsin 53022
Telephone: 800 / DIN-Rail (346-7245)
Fax: 262 / 255-3232
info.us@wago.com
www.wago.us

WAGO Canada Inc.
1550 Yorkton Court, Unit 1
Burlington, ON
L7P 5B7
Telephone: 888 / WAGO 221 (924-6221)
info.ca@wago.com
www.wago.ca

WAGO is registered trademark of WAGO Verwaltungsgesellschaft mbH.
"Copyright - WAGO Kontakttechnik GmbH-Co. KG - all rights reserved. The content and structure of the WAGO Websites, catalogs, videos, and other WAGO media are subject to copyright. The dissemination or changing of the content of these pages and videos is not permitted. Furthermore, the content may neither be copied nor made available to third parties for commercial purposes. Also subject to copyright are the images and videos that were made available to WAGO Kontakttechnik GmbH-Co. KG by third parties."