


BACnet/IP Programmable Fieldbus Controller

32-bit CPU, multitasking



The 750-830 BACnet PLC connects the WAGO-I/O-SYSTEM to the BACnet protocol.

The 750-830 Controller corresponds to BACnet B-BC device profile according to DIN EN ISO 16484-5.

The controller provides the three following functionalities:

- 1. Native server: For each channel, appropriate BACnet objects are generated automatically for the digital, analog input and output modules that are connected to the controller.
- 2. Application server: Other supported BACnet objects can be created via IEC -61131-3 programming environment.
- 3. Application client: Using the client functionality, objects and their properties can be accessed by other BACnet devices.

Access to BACnet/IP networks is provided by the controller's RJ-45 interface. The integrated RS-232 interface communicates with external devices. The controller can also be addressed as Modbus RTU slave via RS-232 interface.


Programming PLC applications is performed in compliance with IEC 61131-3. It is capable of multitasking, has a battery-backed, real-time clock and is based on a 32-bit CPU.

For Web-based applications, HTML pages can be generated on an internal server.

Start-up and configuration of the BACnet networks is performed using the Windows-compliant WAGO BACnet Configurator.

Description	Item No.	Pack. Unit
BACnet/IP Controller	750-830	1
Product discontinuation	Last Call: 31.12.2018	
Product substitutes:	750-831	
Accessories	Item No.	Pack. Unit
WAGO BACnet configurator	see Section 1	
WAGO-I/O-PRO V2.3, RS-232 kit	759-333	1
Miniature WSB Quick marking system		
plain	248-501	5
with marking	see Section 11	
Approvals		
BACnet approvals		
WSPCert certification	ISO 16484-5:2010	
BTL listing	BTL (BACnet® Testing Laboratories)	
Conformity marking	CE	
Korea Certification		
Marine applications	ABS, BV, DNV, GL, KR, LR, NKK, PRS, RINA	
UL 508		
ANSI/ISA 12.12.01	Class I, Div. 2, Grp. ABCD, T4	
TÜV 07 ATEX 554086 X	I M2 Ex d I Mb, II 3 G Ex nA IIC T4 Gc, II 3 D Ex tc IIIC T135°C Dc	
IECEx TUN 09.0001 X	Ex d I Mb, Ex nA IIC T4 Gc, Ex tc IIIC T135°C Dc	

System Data	
System data ETHERNET:	
No. of controllers	limited by network topology
Transmission medium	S-UTP 100 Ω Cat 5
Max. length of fieldbus segment	100 m limited by IEEE 802.3
Max. length of network	acc. to IEEE 802.3 standard
Baud rate	10/100 Mbit/s
Buscoupler connection	RJ-45
Protocols	BACnet/IP, MODBUS/TCP (UDP), HTTP, BootP, DHCP, DNS, SNTP, FTP, SNMP V1, SMTP
System data Serial:	
Transmission medium	Shielded Cu cable 2 (4) x 0.25 mm ²
Max. length of fieldbus segment	15 m depending on baud rate/cable (at 19200 baud)
Baud rate	9600 baud ... 115 200 baud
Buscoupler connection	1 x D-Sub 9; socket
Programming	WAGO-I/O-PRO V2.3
IEC 61131-3	IL, LD, FBD (CFC), ST, FC
BACnet device profile	B-BC (BACnet Building Controller)
BACnet version	1.7



Technical Data	
Number of I/O modules	64
with bus extension	250
Configuration	via PC
Program memory	512 Kbytes
Data memory	256 Kbytes
Non-volatile memory (retain)	24 Kbytes (16 Kbytes retain, 8 Kbytes flag)
Flash	4.5 Mbytes
Power supply	24 V DC (-25 % ... +30 %)
Max. input current (24 V)	500 mA
Power supply efficiency	87 %
Internal current consumption (5 V)	300 mA
Total current for I/O modules (5 V)	1700 mA
Isolation	500 V system/supply
Voltage via power jumper contacts	24 V DC (-25 % ... +30 %)
Current via power jumper contacts (max.)	10 A DC
BACnet implementation acc. to	EN ISO 16484-5 =ANSI/ASHRAE 135-2004
Fieldbus (Modbus/TCP):	
Max. input process image	2 Kbytes
Max. output process image	2 Kbytes
Max. input variables	512 bytes
Max. output variables	512 bytes

General Specifications	
Operating temperature	0 °C ... +55 °C
Wire connection	CAGE CLAMP®
Cross sections	0.08 mm ² ... 2.5 mm ² / AWG 28 ... 14
Strip lengths	8 ... 9 mm / 0.33 in
Dimensions (mm) W x H x L	51 x 65 x 100
	Height from upper-edge of DIN 35 rail
Weight	192.4 g
Storage temperature	-25 °C ... +85 °C
Relative air humidity (no condensation)	95 %
Vibration resistance	acc. to IEC 60068-2-6
Shock resistance	acc. to IEC 60068-2-27
Degree of protection	IP20
EMC immunity of interference	acc. to EN 61000-6-2, marine applications
EMC emission of interference	acc. to EN 61000-6-3, marine applications