


# Power supply Cable

for WAGO  $\equiv$  SPEEDWAY 767



Description	Item no.	Pack. unit pcs																																																				
Power supply cable, not fitted with connectors																																																						
25 m	756-3100/0000-0250	1																																																				
50 m	756-3100/0000-0500	1																																																				
100 m	756-3100/0000-1000	1																																																				
Special lengths on request																																																						
<p><b>Short description:</b></p> <ul style="list-style-type: none"> <li>• PUR, halogen-free</li> <li>• UL / CSA</li> <li>• Drag chain suitability</li> <li>• Free of silicon and CFC</li> <li>• Good resistance to microbes, hydrolysis, oil, ozone and UV radiation. Good chemical resistance.</li> <li>• UL approved</li> </ul>	<p><b>Technical Data</b></p> <table border="1"> <thead> <tr> <th colspan="2">General</th> </tr> </thead> <tbody> <tr><td>Operating voltage</td><td>AC/DC 250 V acc. to IEC 60664-1</td></tr> <tr><td>Operating current</td><td>4 A acc. to IEC 60512-3</td></tr> <tr><td>Rated surge voltage</td><td>2.5 kV acc. to IEC 61076-2-101</td></tr> <tr><td>Insulation resistance</td><td>&gt; 10<sup>9</sup> Ω acc. to IEC 60512-2</td></tr> <tr><td>Contact resistance</td><td>≤ 10 mΩ acc. to IEC 61076-2-101</td></tr> <tr><td>Resistance of conductor</td><td>≤ 26 Ω/km</td></tr> <tr><td>Pollution degree</td><td>3/2 acc. to IEC 60664-1</td></tr> <tr><td>Degree of protection</td><td>IP67 acc. to IEC 60529</td></tr> <tr><td>Operating temperature</td><td>-30 °C ... +80 °C (static and moving)</td></tr> <tr><td colspan="2">Drag chain suitability</td></tr> <tr><td>Min. bending radius</td><td>10 x cable Ø</td></tr> <tr><td>Bending cycles</td><td>≥ 4 million</td></tr> <tr><td>Max. acceleration</td><td>10 m/s<sup>2</sup></td></tr> <tr><td>Max. traversing rate</td><td>4 m/s</td></tr> <tr><td>Max. traverse path</td><td>15 m horizontal</td></tr> <tr><td>Torsion</td><td>max. 360°/m</td></tr> <tr><td colspan="2">Cable</td></tr> <tr><td>Type code</td><td>Lif9YH-11YH 4x0.75 mm<sup>2</sup></td></tr> <tr><td>Note</td><td>Construction acc. to UL + CSA</td></tr> <tr><td>Conductor</td><td>Bare copper wire (40 x 0.15 mm)</td></tr> <tr><td>Insulation</td><td>Halogen-free PP9Y</td></tr> <tr><td></td><td>Halogen-free polyurethane (PUR) acc. to VDE 0250 part 818, flame resistant acc. to VDE 0472 part 804/B</td></tr> <tr><td>Lead Color</td><td>brown, white, blue, black</td></tr> <tr><td>Color</td><td>Gray (~ RAL 7040)</td></tr> <tr><td>Cable diameter</td><td>Ø 6.2 mm ± 0.2</td></tr> </tbody> </table>		General		Operating voltage	AC/DC 250 V acc. to IEC 60664-1	Operating current	4 A acc. to IEC 60512-3	Rated surge voltage	2.5 kV acc. to IEC 61076-2-101	Insulation resistance	> 10 <sup>9</sup> Ω acc. to IEC 60512-2	Contact resistance	≤ 10 mΩ acc. to IEC 61076-2-101	Resistance of conductor	≤ 26 Ω/km	Pollution degree	3/2 acc. to IEC 60664-1	Degree of protection	IP67 acc. to IEC 60529	Operating temperature	-30 °C ... +80 °C (static and moving)	Drag chain suitability		Min. bending radius	10 x cable Ø	Bending cycles	≥ 4 million	Max. acceleration	10 m/s <sup>2</sup>	Max. traversing rate	4 m/s	Max. traverse path	15 m horizontal	Torsion	max. 360°/m	Cable		Type code	Lif9YH-11YH 4x0.75 mm <sup>2</sup>	Note	Construction acc. to UL + CSA	Conductor	Bare copper wire (40 x 0.15 mm)	Insulation	Halogen-free PP9Y		Halogen-free polyurethane (PUR) acc. to VDE 0250 part 818, flame resistant acc. to VDE 0472 part 804/B	Lead Color	brown, white, blue, black	Color	Gray (~ RAL 7040)	Cable diameter	Ø 6.2 mm ± 0.2
General																																																						
Operating voltage	AC/DC 250 V acc. to IEC 60664-1																																																					
Operating current	4 A acc. to IEC 60512-3																																																					
Rated surge voltage	2.5 kV acc. to IEC 61076-2-101																																																					
Insulation resistance	> 10 <sup>9</sup> Ω acc. to IEC 60512-2																																																					
Contact resistance	≤ 10 mΩ acc. to IEC 61076-2-101																																																					
Resistance of conductor	≤ 26 Ω/km																																																					
Pollution degree	3/2 acc. to IEC 60664-1																																																					
Degree of protection	IP67 acc. to IEC 60529																																																					
Operating temperature	-30 °C ... +80 °C (static and moving)																																																					
Drag chain suitability																																																						
Min. bending radius	10 x cable Ø																																																					
Bending cycles	≥ 4 million																																																					
Max. acceleration	10 m/s <sup>2</sup>																																																					
Max. traversing rate	4 m/s																																																					
Max. traverse path	15 m horizontal																																																					
Torsion	max. 360°/m																																																					
Cable																																																						
Type code	Lif9YH-11YH 4x0.75 mm <sup>2</sup>																																																					
Note	Construction acc. to UL + CSA																																																					
Conductor	Bare copper wire (40 x 0.15 mm)																																																					
Insulation	Halogen-free PP9Y																																																					
	Halogen-free polyurethane (PUR) acc. to VDE 0250 part 818, flame resistant acc. to VDE 0472 part 804/B																																																					
Lead Color	brown, white, blue, black																																																					
Color	Gray (~ RAL 7040)																																																					
Cable diameter	Ø 6.2 mm ± 0.2																																																					