


M12 PROFIBUS / S-BUS socket, straight

1/1

Data Sheet


Description	Item no.	Pack. unit pcs
M12 socket, B-coded, straight, 5-poles, shielded, scw technology	756-9412/060-000	1

Mounting	Technical data																									
	General																									
	<table border="0"> <tr><td>Housing material</td><td>Zinc die casting</td></tr> <tr><td>Housing surface</td><td>Nickel plated</td></tr> <tr><td>Contact material</td><td>brass (CuZn)</td></tr> <tr><td>Insert material</td><td>PA</td></tr> <tr><td>Contact plating</td><td>Gold (Au)</td></tr> <tr><td>Type of connection</td><td>Screw</td></tr> <tr><td>Seal</td><td>Neoprene</td></tr> <tr><td>O-Ring</td><td>Viton</td></tr> <tr><td>Temperature range</td><td>-40 °C ... +85 °C</td></tr> <tr><td>Cable entry</td><td>Ø 6-8 mm</td></tr> <tr><td>Kind of locking</td><td>Screw locking M12</td></tr> <tr><td>Mating cycles</td><td>100</td></tr> <tr><td>Class of protection</td><td>IP67 in locked position</td></tr> </table>	Housing material	Zinc die casting	Housing surface	Nickel plated	Contact material	brass (CuZn)	Insert material	PA	Contact plating	Gold (Au)	Type of connection	Screw	Seal	Neoprene	O-Ring	Viton	Temperature range	-40 °C ... +85 °C	Cable entry	Ø 6-8 mm	Kind of locking	Screw locking M12	Mating cycles	100	Class of protection
Housing material	Zinc die casting																									
Housing surface	Nickel plated																									
Contact material	brass (CuZn)																									
Insert material	PA																									
Contact plating	Gold (Au)																									
Type of connection	Screw																									
Seal	Neoprene																									
O-Ring	Viton																									
Temperature range	-40 °C ... +85 °C																									
Cable entry	Ø 6-8 mm																									
Kind of locking	Screw locking M12																									
Mating cycles	100																									
Class of protection	IP67 in locked position																									
	Electrical data:																									
	<table border="0"> <tr><td>Pole number</td><td>5</td></tr> <tr><td>Conductor size</td><td>max. 0.75 mm² (AWG 20)</td></tr> <tr><td>Rated current</td><td>4 A (40 °C)</td></tr> <tr><td>Rated voltage</td><td>125 V</td></tr> <tr><td>Test voltage</td><td>1.5 kV AC</td></tr> <tr><td>Overvoltage category</td><td>II</td></tr> <tr><td>Material group</td><td>III</td></tr> <tr><td>Transition resistance</td><td>≤3 mΩ</td></tr> <tr><td>Pollution degree</td><td>3</td></tr> </table>	Pole number	5	Conductor size	max. 0.75 mm ² (AWG 20)	Rated current	4 A (40 °C)	Rated voltage	125 V	Test voltage	1.5 kV AC	Overvoltage category	II	Material group	III	Transition resistance	≤3 mΩ	Pollution degree	3							
Pole number	5																									
Conductor size	max. 0.75 mm ² (AWG 20)																									
Rated current	4 A (40 °C)																									
Rated voltage	125 V																									
Test voltage	1.5 kV AC																									
Overvoltage category	II																									
Material group	III																									
Transition resistance	≤3 mΩ																									
Pollution degree	3																									
	Note:																									
	Assembling S-bus ¹ lines requires the four ground conductors to be crimped together in a 0.75 mm ² ferrule and connected to pin 5.																									
	1) S-bus = Systembus																									