


TO-PASS® Telecontrol Module M

Telecontrol module for fault detection/indication, monitoring and remote control



Universal telecontrol module for fault detection/indication and monitoring of machines and installations over a GSM network. The module can be used in many countries via an integrated quad-band GSM modem. Messages are sent via SMS, e-mail, fax or phone call. Switching of outputs is performed via SMS. 8 digital inputs, 4 digital outputs with integrated GSM modem. Ideal for applications in distributed stations for temperatures ranging from -20 °C to +70 °C. Ability to mount on DIN-rail and intuitive user software make unit easy to handle. Operating voltage ranges from 8.5 to 36VDC.

Special functions:

- Acknowledgment: Acknowledging any fault message
- Stand-by: Automatic remote switching of the stand-by service
- Remote parametrization: Programming and remote control conveniently performed from the office

LED indicators:

- Continuous "Com" + "Busy" + "Run" LED: CSD connection/communication initialization phase approx. 50 sec.
- Continuous "Busy" + "Run" LED: Active mode
- "Run" LED 2 Hz: Error
- "Run" LED 0.5 Hz: Ready for operation

Description	Item No.	Pack. Unit
Telecontrol Module M	761-200	1
Product discontinued!		
Last call:	28.02.2011	
Substitute:	761-210	
Accessories		
Antennas, USB adapter, GSM modem and power supply units	see page 371	
Approvals		
Approvals	for all EU countries	
	Approvals for other countries on request	

Technical Data	
Number of inputs	Digital: 8 (6.5 V ... 24 V)
No. of outputs	Digital: 4 contacts
Number of receivers	4 (PC, SMS, e-mail, phone, fax)
Communication	GSM quad-band
Communication types	SMS (bidirectional), telecommunication dial-up connection (CSD)
Operating voltage	8.5 V ... 36 V DC
Closed current	40 mA
Current during transmission	< 600 mA
Max. input current (24 V)	1.6 mA
Load of digital outputs	36 V DC/0.5 A
Operating temperature	-20 °C ... +70 °C
Type of mounting	DIN 35 rail
Wire connection	Terminal strips with push-wire connection (WAGO 250 Series)
Cross sections	0.5 mm ² ... 1.5 mm ² / AWG 22 ... 14
Stripped lengths	9 mm / 0.35 in
Dimensions (mm) W x H x L	109 x 105 x 78
Weight	485.31 g
Storage temperature	-20 °C ... +70 °C
Degree of protection	IP20
Antenna connection	SMA (version 2 and higher), FME (up to version 1)