

Relay Socket with Small Switching Relay


1/2


Socket with relay (2 changeover contacts) and status indication

Data sheet



Similar photo



Description	Item-No.	Pack.-unit pcs																																																						
Socket with relay, AC 115 V, 2 changeover contacts	788-515	1																																																						
- Relay socket for DIN 35 carrier rails. - Status indication through pluggable LED module (red). - Insulated, pluggable jumper system suitable for both coil and load side. - CAGE CLAMP® S connection. Solid wires, fine-stranded wires with crimped ferrules or ultrasonically bonded wire ends can be inserted directly. - Quick exchange of the relay and the status indication during maintenance, without having to detach the wiring. - Safe electrical isolation in accordance with DIN VDE 0140 Part 1. DC-Load limiting value graph  Note: Inductive loads have to be attenuated by an appropriate protective circuit in order to protect relay coils and contacts ! Technical Data <table><tr><td>Contact material</td><td>AgNi 90/10</td></tr><tr><td>Input nominal voltage U_N</td><td>AC 115 V</td></tr><tr><td>Input voltage range</td><td>U_N ± 10 %</td></tr><tr><td>Current input at U_N (20 °C)</td><td>8 mA</td></tr><tr><td>Max. switching voltage</td><td>AC 250 V</td></tr><tr><td>Max. making current (resistive)</td><td></td></tr><tr><td>at 10 % continuous duty</td><td>4 s (AC) 15 A</td></tr><tr><td>Max. continuous current</td><td>2 x 8 A</td></tr><tr><td>Max. switching power</td><td></td></tr><tr><td>(resistive)</td><td>2 x AC 2000 VA</td></tr><tr><td>(resistive)</td><td>DC see load limiting value graph</td></tr><tr><td>Max. number of switching operations with/without load</td><td>6 min⁻¹ / 1200 min⁻¹</td></tr><tr><td>Operating power</td><td>0.75 VA</td></tr><tr><td>Pull-in/dropout/bounce time_{typ.}</td><td>7 ms / 2 ms / 3 ms</td></tr><tr><td>Operation at normal rating</td><td>100 % continuous duty</td></tr><tr><td>Dielectric strength</td><td></td></tr><tr><td>contact/coil</td><td>5 kV</td></tr><tr><td>open contact</td><td>1 kV</td></tr><tr><td>Nominal voltage acc. to VDE 0110 Part1 / 4.97</td><td></td></tr><tr><td>IEC 60664-1</td><td>250 V / 4 kV / 3</td></tr><tr><td>Mechanical life</td><td>5 x 10⁸ switching operations</td></tr><tr><td>Degree of protection</td><td>IP 20</td></tr><tr><td>Relay type</td><td>RT 2</td></tr><tr><td>Ambient operating temperature</td><td>-25 °C ... +50 °C</td></tr><tr><td>Storage temperature</td><td>-40 °C ... +70 °C</td></tr><tr><td>Dimensions (WxHxD)</td><td>(15x53*x86) mm / (0.59x2.09x3.39) in</td></tr><tr><td></td><td>* from upper edge of DIN 35 rail</td></tr></table>			Contact material	AgNi 90/10	Input nominal voltage U _N	AC 115 V	Input voltage range	U _N ± 10 %	Current input at U _N (20 °C)	8 mA	Max. switching voltage	AC 250 V	Max. making current (resistive)		at 10 % continuous duty	4 s (AC) 15 A	Max. continuous current	2 x 8 A	Max. switching power		(resistive)	2 x AC 2000 VA	(resistive)	DC see load limiting value graph	Max. number of switching operations with/without load	6 min ⁻¹ / 1200 min ⁻¹	Operating power	0.75 VA	Pull-in/dropout/bounce time _{typ.}	7 ms / 2 ms / 3 ms	Operation at normal rating	100 % continuous duty	Dielectric strength		contact/coil	5 kV	open contact	1 kV	Nominal voltage acc. to VDE 0110 Part1 / 4.97		IEC 60664-1	250 V / 4 kV / 3	Mechanical life	5 x 10 ⁸ switching operations	Degree of protection	IP 20	Relay type	RT 2	Ambient operating temperature	-25 °C ... +50 °C	Storage temperature	-40 °C ... +70 °C	Dimensions (WxHxD)	(15x53*x86) mm / (0.59x2.09x3.39) in		* from upper edge of DIN 35 rail
Contact material	AgNi 90/10																																																							
Input nominal voltage U _N	AC 115 V																																																							
Input voltage range	U _N ± 10 %																																																							
Current input at U _N (20 °C)	8 mA																																																							
Max. switching voltage	AC 250 V																																																							
Max. making current (resistive)																																																								
at 10 % continuous duty	4 s (AC) 15 A																																																							
Max. continuous current	2 x 8 A																																																							
Max. switching power																																																								
(resistive)	2 x AC 2000 VA																																																							
(resistive)	DC see load limiting value graph																																																							
Max. number of switching operations with/without load	6 min ⁻¹ / 1200 min ⁻¹																																																							
Operating power	0.75 VA																																																							
Pull-in/dropout/bounce time _{typ.}	7 ms / 2 ms / 3 ms																																																							
Operation at normal rating	100 % continuous duty																																																							
Dielectric strength																																																								
contact/coil	5 kV																																																							
open contact	1 kV																																																							
Nominal voltage acc. to VDE 0110 Part1 / 4.97																																																								
IEC 60664-1	250 V / 4 kV / 3																																																							
Mechanical life	5 x 10 ⁸ switching operations																																																							
Degree of protection	IP 20																																																							
Relay type	RT 2																																																							
Ambient operating temperature	-25 °C ... +50 °C																																																							
Storage temperature	-40 °C ... +70 °C																																																							
Dimensions (WxHxD)	(15x53*x86) mm / (0.59x2.09x3.39) in																																																							
	* from upper edge of DIN 35 rail																																																							

Relay Socket with Small Switching Relay


2/2

Socket with relay (2 changeover contacts) and status indication

Data sheet


Commoning possibilities on the contact side:

- relay internal contacts 11/21
- relay spanning contacts 11/11



Commoning possibilities on the coil side:

- contacts A2/A2



Wire connection	CAGE CLAMP® S
	0,34-2,5 mm² / AWG 22-12
Stripped length	9-10 mm / 0.37 in
Standards / prescriptions	DIN VDE 0140 Part1, DIN EN 61140 DIN VDE 0160, EN 50178 Class of protection II
Approvals	cUL _{us} UL508 / CSA22.2 E175199 Only use replacement relay 788-176 for UL applications (see accessories)
Accessories:	
Comb type jumper bar	
18 A, 2-way	788-113
18 A, 3-way	788-114
18 A, 4-way	788-115
18 A, 6-way	788-116
18 A, 8-way	788-117
18 A, 2-way	859-402
Operation indication AC 115 V	788-124
Relay RT2, 2 CO	788-176
WMB Multi marking system	(General catalogue W3 Vol.1 Chapt.8)