


Industrial Managed Switch; 8 Ports 100BASE-TX; PROFINET; Extended Temperature Range



The configurable 852-602 Industrial Switch is a managed ETHERNET switch equipped with eight 10/100BASE-TX copper ports. Packaged in a rugged housing, this switch offers both a redundant power supply and relay-based function monitoring. The PROFINET certificate (conformity class B) guarantees easy integration into PROFINET automation systems using the device description file (GSD). In addition, the device supports the "PROFINET Netload Class II."

The device supports flexible multi-port mirroring configuration via device description file or Web-based management. Function blocks allow cyclic PROFINET switch diagnostics to be efficiently implemented within the TIA Portal. An application note that outlines this process is available.

Features:

- Web-based/SNMP management
- Redundant DC power supply

- Power supply range: 12 ... 60 VDC
- DIP switches to set alarm functions
- Full compliance with IEEE802.3, 802.3u, 802.3x, 802.1d, 802.1w, 802.1s, 802.1Q, 802.1p standards
- Media redundancy protocol (MRP) as manager (MRM) or client (MRC), redundant ring
- Non-blocking, store-and-forward switching, rapid spanning tree protocol (RSTP)
- Autonegotiation and AUTO-MDI/MDIX (crossover)
- VLAN (802.1Q) VID
- IGMP snooping
- Port configuration, status, statistics
- Port trunking and multi-port mirroring
- SNMP v1/v2c/v3 and RMON
- Time synchronization via SNTP
- Storm control, bandwidth limitation and loop detection

Description	Item No.	Pack. Unit
Industrial Managed Switch; 8Port 100BASE-TX; PROFINET; T	852-602	1
Approvals		
Conformity marking	CE	
Ⓢ E175199 Ordinary Locations	UL 61010-2-201	
Technical Data		
MAC table	Up to 16000 addresses	
VLAN	Port-based and tag-based (4k VIDs)	
Jumbo frame size	10 KB	
Supply voltage	12 ... 60 VDC	
Power consumption (max.)	12 W	
ESD (contact/air discharge)	8 KV / 15 KV	
Surrounding air temperature (operation)	-40 ... +70 °C	
Surrounding air temperature (storage)	-40 ... +80 °C	
Protection type	IP30	
Relative humidity (without condensation)	10 ... 95 %	
Dimensions (mm) W x H x D	50 x 162 x 122	
Mounting	Depth from upper-edge of DIN-rail	
Weight	882 g	
Vibration resistance	Per IEC 60068-2-6	
Shock resistance	Per IEC 60068-2-27	
Protection type	IP30	
EMC immunity to interference	Per EN 61000-6-2	
EMC emission of interference	per EN 61000-6-4	

Technical Data	
Switching mode	Store-and-forward; non-blocking
Number of copper ports	8 x 10/100BASE-TX (RJ-45)
Communication standards	IEEE 802.3 10BASE-T IEEE 802.3u 100BASE-TX IEEE 802.3x Flow Control IEEE 802.1d Spanning Tree Protocol (STP) IEEE 802.1w Rapid Spanning Tree Protocol (RSTP) IEEE 802.1s Multiple Spanning Tree Protocol (MSTP) IEEE 802.1Q VLAN Tagging IEEE 802.1p Class of Service IEEE 802.1ab Link Layer Discovery Protocol (LLDP) PROFINET Conformance Class B
Redundancy functions	Redundant DC power supply; STP; RSTP; MSTP; Media redundancy protocol as manager or client
Configuration	DIP switch for signal contact; Web-based CLI; SNMPv1/v2/v3
Diagnostics	Signal contact; Port status; Port statistics; Port load; Traffic monitor; SFP information; Syslog; SNMP traps; PN diagnostics (cyclic and acyclic)
Firmware update	Web-based management; CLI with TFTP server
PROFINET	PROFINET Device; PROFINET Conformance Class B; Netload Class II; Media redundancy protocol (MRP) as manager (MRM) or client (MRC); PNIO Version V2.32; Identification & Maintenance Functions