


WAGO I/O System 750/753

Supply Filter; 24 VDC

750-626; 750-626/025-000



© 2026 WAGO GmbH & Co. KG
All rights reserved.

WAGO GmbH & Co. KG

Hansastraße 27

D - 32423 Minden

Phone: +49 571/887 – 0

E-Mail: ✉ info@wago.comInternet: 🌐 www.wago.com**Technical Support**

Phone: +49 571/887 – 44555

E-Mail: ✉ support@wago.comInternet: 🌐 www.wago.com/support

Every conceivable measure has been taken to ensure the accuracy and completeness of this documentation. However, as errors can never be fully excluded, we always appreciate any information or suggestions for improving the documentation.

E-Mail: ✉ documentation@wago.com

We wish to point out that the software and hardware terms as well as the trademarks of companies used and/or mentioned in the present documentation are generally protected by trademark or patent.

WAGO is a registered trademark of WAGO Verwaltungsgesellschaft mbH.

Table of Contents

- 1 Provisions..... 4**
 - 1.1 Scope of Applicability 4
- 2 Overview..... 5**
- 3 Properties..... 6**
 - 3.1 View..... 6
 - 3.2 Indicators..... 7
 - 3.3 Wiring Interface..... 7
 - 3.4 Power Jumper Contacts..... 8
 - 3.5 Schematic Circuit Diagram 9
- 4 Planning..... 10**
 - 4.1 Compatibility..... 10
 - 4.2 Requirements for Wiring and Accessories 10
- 5 Appendix 11**
 - 5.1 Technical Data, Approvals, Guidelines and Standards..... 11
 - 5.1.1 Data sheet 750-626..... 12
 - 5.1.2 Data sheet 750-626/025-000..... 15

1 Provisions

1.1 Scope of Applicability

This document applies to the following products:

🔗 **750-626** (24V DC Supply Filter (Surge)) Supply Filter; 24 VDC.

From hardware version	05
From firmware version	--
Product detail page	🔗 www.wago.com/750-626

🔗 **750-626/025-000** (24V DC Supply Filter (Surge) /T) Supply Filter; 24 VDC; ext. temperature.

From hardware version	04
From firmware version	--
Product detail page	🔗 www.wago.com/750-626/025-000

i Note

Note applicable documents!

The complete operating instructions for the products consist of several applicable documents. The products must only be installed and operated in accordance with the complete operating instructions. Knowledge of all applicable documents is required for proper use. Please find all documents and information on the detailed product pages.

Applicable document

☐ **System Manual I/O System 750/753**

- Provisions
- Safety
- Planning
- Transport and Storage
- Assembly and Disassembly
- Conductor Termination
- Decommissioning

2 Overview

The supply filter module is used to provide both the 24 V system voltage and 24 V field supply voltage to a fieldbus node.

It contains a filter for the 24 V system supply and protection against transient overvoltages for the system supply and field supply via the power jumper contacts.

Use of filter modules also allows the WAGO I/O System 750/753 to be used in shipbuilding or offshore/onshore areas (e.g., platforms and loading facilities). This is demonstrated by compliance with the requirements of leading classification agencies, such as the Germanischer Lloyd and Lloyd's Register. The filter module ensures proper (certified) system operation.

The standard version of the filter module is also intended for marine-certified operation in conjunction with an Ex i supply module (item no.: [750-625/000-001](#)) or for use with PROFIsafe modules.

The filter module has no blade contacts to receive a supply voltage; it is powered by an external source via CAGE CLAMP® connections.

The filter module provides the 24 V field supply voltage for the field level to downstream I/O modules via its spring contacts. The 24 V supply voltage for the system supply is provided via CAGE CLAMP® connections.

Two green status LEDs indicate the status of the power supply for the system supply and field supply, respectively.

3 Properties

3.1 View




Figure 1: View

1	Slot for Mini-WSB (optional)	System Manual I/O System 750/753
2	Status LEDs	Indicators [> 7]
3	Data contacts	System Manual I/O System 750/753
4	Access to open the associated CAGE CLAMP® connection	System Manual I/O System 750/753
5	CAGE CLAMP® connection	Wiring Interface [> 7] and System Manual I/O System 750/753
6	Power jumper contacts (spring)	Power Jumper Contacts [> 8] and System Manual I/O System 750/753
7	Release tab	System Manual I/O System 750/753
8	Item number	Scope of Applicability [> 4]

3.2 Indicators

Two green status LEDs indicate the status of the power supply for the system supply and field supply, respectively.




Figure 2: Indicators

Name	LED	Status	Function
Status of the operating voltage – System supply	A	Off	No 24 V operating voltage for the system supply
		Green	24 V operating voltage available for the system supply
Status of the operating voltage – Power jumper contacts	B ^{*)}	Off	No 24 V operating voltage at the power jumper contacts
		Green	24 V operating voltage applied to the power jumper contacts

*) LED position is production-dependent; up to hardware 02: LED C

3.3 Wiring Interface




Figure 3: CAGE CLAMP® Connections

Designation	Connection	Function
24 V OUT, system	1	Output, system supply, 24 V (filtered)
0 V OUT, system	5	Output, system supply, 0 V (filtered)
24 V IN, field	2	Feed-in, field supply, 24 V
	6	
0 V IN, field	3	Feed-in, field supply, 0 V
	8	
24 V IN, system	4	Feed-in, system supply, 24 V
0 V IN, system	8	Feed-in, system supply, 0 V

3.4 Power Jumper Contacts

The potential for the field supply is fed in via the spring contacts.

For additional information on the Power Jumper Contacts, please see [System Manual I/O System 750/753](#).




Figure 4: Power Jumper Contacts

Pos.	Type
1	Groove with spring contact
2	

Arrangement in the Bus Node

For electrical compatibility requirements see Section [Schematic Circuit Diagram \[> 9 \]](#).

3.5 Schematic Circuit Diagram




Figure 5: Schematic Circuit Diagram

4 Planning

This section provides helpful information for planning the use of the product in a node.

4.1 Compatibility

The filter module can be operated on all head stations of the WAGO I/O System 750/753.

4.2 Requirements for Wiring and Accessories

The standard version of the filter module is also intended for marine-certified operation in conjunction with an Ex i supply module (item no.: [750-625/000-001](#)) or for use with PROFIsafe modules.

For power supply concepts and the node structure, e.g., for certified operation of the filter module in shipbuilding or onshore/offshore applications, see the [System Manual I/O System 750/753](#).

5 Appendix



5.1 Technical Data, Approvals, Guidelines and Standards

Note

Subject to changes!

Please also observe the further product documentation! You can generate the current datasheet at any time at: www.wago.com /<item number>.

See also

-  Data sheet 750-626 [▶ 12]
-  Data sheet 750-626/025-000 [▶ 15]

Technical data

Signal type	Voltage
Signal type (voltage)	24 VDC
Supply voltage (system)	24 VDC (-25 ... +30 %); Via wiring interface (CAGE CLAMP® connection); External fuse required: 2 A slow-blow
Supply voltage (field)	24 VDC (-25 ... +30 %); Via power jumper contacts (supply via CAGE CLAMP® connection; distribution via spring contact); External fuse required: 10 A slow-blow
Current via system voltage (max.)	1.5 A (1 A up to hardware version 04)
Current carrying capacity (power jumper contacts)	10 A
Number of outgoing power jumper contacts	2
Use	Marine-certified operation in conjunction with the Ex i supply module and the use of 750 Series PROFIsafe Modules
Indicators	LED (A, B) green: operating voltage status: system, power jumper contacts

Connection data

Connectable conductor materials	Copper
Connection type	System/field supply
Solid conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Fine-stranded conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches
Connection technology: field supply	4 x CAGE CLAMP®
Connection technology: system supply	4 x CAGE CLAMP®

Physical data

Width	12 mm / 0.472 inches
Height	100 mm / 3.937 inches
Depth	69.8 mm / 2.748 inches
Depth from upper-edge of DIN-rail	62.6 mm / 2.465 inches

Mechanical data

Mounting type	DIN-35 rail
Pluggable connector	fixed

Material data

Color	light gray
Housing material	Polycarbonate; polyamide 6.6
Fire load	1.096 MJ
Weight	49.6 g
Conformity marking	CE

Environmental requirements

Ambient temperature (operation)	0 ... +55 °C
Ambient temperature (storage)	-40 ... +85 °C
Protection type	IP20
Pollution degree	2 per IEC 61131-2
Operating altitude	0 ... 2000 m / 0 ... 6562 ft
Mounting position	Horizontal left, horizontal right, horizontal top, horizontal bottom, vertical top and vertical bottom
Relative humidity (without condensation)	95 %
Vibration resistance	4g per IEC 60068-2-6
Shock resistance	15g per IEC 60068-2-27
EMC immunity to interference	per EN 61000-6-2, marine applications
EMC emission of interference	per EN 61000-6-4, marine applications
Exposure to pollutants	per IEC 60068-2-42 and IEC 60068-2-43
Permissible H ₂ S contaminant concentration at a relative humidity 75 %	10 ppm
Permissible SO ₂ contaminant concentration at a relative humidity 75 %	25 ppm

Product Classification

UNSPSC	39121610
eCl@ss 10.0	27-24-26-10
eCl@ss 9.0	27-24-26-10
ETIM 9.0	EC001600
ETIM 10.0	EC001600
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

CAS-No.	1303-86-2 1317-36-8 7439-92-1
REACH Candidate List Substance	Diboron trioxide Lead Lead monoxide
RoHS Compliance Status	Compliant,With Exemption
RoHS Exemption	7(a) 7(c)-I
SCIP notification number (Austria)	67c0c0b1-7384-4b47-a2e5-4c27138899d5
SCIP notification number (Belgium)	df0f77b2-d61d-4ad6-a3b3-f7711ef98d42
SCIP notification number (Bulgaria)	2d06e6ca-d722-4510-b42c-65e6403fa9d5
SCIP notification number (Czech Republic)	a68e4cdd-5f5a-418b-8e5e-e803e77fca65
SCIP notification number (Denmark)	64efa0c4-e047-4e42-be2c-7ac2c5682a5f
SCIP notification number (Finland)	1d58eed1-1e70-4a5c-b275-94ef51c4b0e6
SCIP notification number (France)	4e0a8b03-54ed-4246-ae5c-7b0f6059a324
SCIP notification number (Germany)	44af5fb9-ca85-4975-b391-63f66ebec7da
SCIP notification number (Hungary)	96033c53-5b69-4a96-822d-d0cd90af0ac2
SCIP notification number (Italy)	cf47825e-5dc0-4974-bde0-53ea3b2effe4
SCIP notification number (Netherlands)	aae1ec69-6acb-4163-9a02-4744f8d8f656
SCIP notification number (Poland)	2e19eca4-0e0c-4291-a245-0b850a9e3ac2
SCIP notification number (Romania)	4edd15ad-8a94-49aa-bbc0-cf5351cee8b9
SCIP notification number (Sweden)	caf61d73-0270-4183-8472-a7cf01e7c216

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 020/2011	EAC CoC 03083
KC National Radio Research Agency	Article 58-2, Clause 3	MSIP-REM-W43-IDE750
UL Underwriters Laboratories Inc. (ORDINARY LOCATIONS)	UL 508	E175199

Declarations of conformity and manufacturer's declarations

Approval	Standard	Certificate Name
EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
UK-Declaration of Conformity WAGO GmbH & Co. KG	-	-

Approvals for marine applications



Approval	Standard	Certificate Name
ABS American Bureau of Shipping	-	22-2219060
BSH Bundesamt fuer Seeschifffahrt und Hydrographie	-	1104
BV Bureau Veritas S.A.	-	13453/E0 BV
DNV DNV GL SE	DNV-CG-0339, Aug. 2021	TAA0000194
KR Korean Register of Shipping	-	KR HMB05880-AC001
LR Lloyds Register EMEA	-	LR22180952TA
PRS Polski Rejestr Statków	-	TE/1101/880590/23
RINA RINA Germany GmbH	-	ELE343521XG001

Approvals for hazardous areas



Approval	Standard	Certificate Name
ATEX TUEV Nord Cert GmbH	EN 60079-0	TUEV14ATEX148929X (II 3 G Ex ec IIC T4 Gc)
CCCEX CQST/CNEX	CNCA-C23-01	2020312310000213 (Ex ec IIC T4 Gc)
IECEX TUEV Nord Cert GmbH	IEC 60079-0	IECEX TUN 14.0035 X (Ex ec IIC T4 Gc)
INMETRO TUV Rheinland do Brasil Ltda.	IEC 60079-0	TUV 12.1297 X
KTL Korea Testing Laboratory	KOSHA Article 34, IEC60079-0	21-KA4BO-0554X
UKEx WAGO GmbH & Co. KG	EN 60079-0	UKCA_WA GO22UKEX003X_ec
UL Underwriters Laboratories Inc. (HAZARDOUS LOCATIONS)	UL 121201	E198726

Technical data

Signal type	Voltage
Signal type (voltage)	24 VDC
Supply voltage (system)	24 VDC (-25 ... +30 %); via pluggable connector (CAGE CLAMP® connection)
Supply voltage (field)	24 VDC (-25 ... +30 %); via power jumper contacts (power supply via CAGE CLAMP® connection; transmission (field-side supply voltage only) via spring contact
Current via system voltage (max.)	1.5 A (1 A up to hardware 04)
Current carrying capacity (power jumper contacts)	10 A
Number of outgoing power jumper contacts	2
Use	Marine-certified operation in conjunction with the Ex i supply module and the use of 750 Series PROFIsafe Modules
Indicators	LED (A, B) green: operating voltage status: system, power jumper contacts

Connection Data

Connectable conductor materials	Copper
Connection type	System/field supply
Solid conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Fine-stranded conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches
Connection technology: field supply	4 x CAGE CLAMP®
Connection technology: system supply	4 x CAGE CLAMP®

Physical data

Width	12 mm / 0.472 inches
Height	100 mm / 3.937 inches
Depth	69.8 mm / 2.748 inches
Depth from upper-edge of DIN-rail	62.6 mm / 2.465 inches

Mechanical data

Mounting type	DIN-35 rail
Pluggable connector	fixed

Material data

Color	light gray
Housing material	Polycarbonate; polyamide 6.6
Fire load	0.767 MJ
Weight	50.6 g
Conformity marking	CE

Environmental requirements

Ambient temperature (operation)	-20 ... +60 °C
Ambient temperature (storage)	-40 ... +85 °C
Protection type	IP20
Pollution degree	2 per IEC 61131-2
Operating altitude	0 ... 2000 m / 0 ... 6562 ft
Mounting position	Horizontal left, horizontal right, horizontal top, horizontal bottom, vertical top and vertical bottom
Relative humidity (without condensation)	95 %
Relative humidity (with condensation)	Short-term condensation per Class 3K6/IEC EN 60721-3-3 and E-DIN 40046-721-3, accounting for a temperature range of -20 to +60 °C (except for wind-driven precipitation, water and ice formation)
Vibration resistance	4g per IEC 60068-2-6
Shock resistance	15g per IEC 60068-2-27
EMC immunity to interference	per EN 61000-6-2, marine applications
EMC emission of interference	per EN 61000-6-4, marine applications
Exposure to pollutants	per IEC 60068-2-42 and IEC 60068-2-43
Permissible H ₂ S contaminant concentration at a relative humidity 75 %	10 ppm
Permissible SO ₂ contaminant concentration at a relative humidity 75 %	25 ppm

Product Classification

UNSPSC	39121610
eCl@ss 10.0	27-24-26-10
eCl@ss 9.0	27-24-26-10
ETIM 9.0	EC001600
ETIM 10.0	EC001600
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

CAS-No.	1303-86-2 1317-36-8 7439-92-1
REACH Candidate List Substance	Diboron trioxide Lead Lead monoxide
RoHS Compliance Status	Compliant,With Exemption
RoHS Exemption	7(a) 7(c)-I
SCIP notification number (Austria)	e6fd8573-3b7a-4f36-a8b5-136d60718724
SCIP notification number (Belgium)	01be08d6-043a-4586-9824-2aefc7bc9e40
SCIP notification number (Bulgaria)	7b3dec9f-500b-49c9-822f-969bf5034032
SCIP notification number (Czech Republic)	8e730349-54ab-4b3b-ae6f-3c2ad7b4bfd0
SCIP notification number (Denmark)	58c0fad2-80b9-4404-ae18-cadac77c043c
SCIP notification number (Finland)	70b8776b-7cad-4f8a-ae1b-52f638e5ff9a
SCIP notification number (France)	4f6ad03a-5e94-433b-9aa4-f7900324f92a
SCIP notification number (Germany)	59939bf1-d4ed-48b6-b4b4-6d3824234118
SCIP notification number (Hungary)	9d47b176-fbb0-4930-9f8d-50ceb1608037
SCIP notification number (Italy)	f92deb57-c832-489d-95d5-081b8cb934dd
SCIP notification number (Netherlands)	e0dac868-2699-45ec-b43a-3fee61e82a93
SCIP notification number (Poland)	c691b10b-415f-4088-9176-826c2d850cc4
SCIP notification number (Romania)	eeb245d0-304c-4056-b484-c0ed4a53dc9f
SCIP notification number (Sweden)	041d9513-0ba6-4f14-ab91-c51566f92f62

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 020/2011	EAC CoC 03083
KC National Radio Research Agency	Article 58-2, Clause 3	MSIP-REM-W43-IDE750
UL Underwriters Laboratories Inc. (ORDINARY LOCATIONS)	UL 508	E175199

Declarations of conformity and manufacturer's declarations

Approval Standard Certificate Name

EU-Declaration of Conformity
WAGO GmbH & Co. KG

-

-

UK-Declaration of Conformity
WAGO GmbH & Co. KG

-

-

Approvals for marine applications



Approval	Standard	Certificate Name
ABS American Bureau of Shipping	-	22-2227356-PDA
BSH Bundesamt fuer Seeschifffahrt und Hydrographie	-	1104
DNV DNV Germany GmbH	DNV-CG-0339, Aug. 2021	TAA00001J4
LR Lloyds Register	-	LR2475997TA
PRS Polski Rejestr Statków	-	TE/1102/880590/23

Approvals for hazardous areas



Approval Standard Certificate Name

ATEX
TUEV Nord Cert GmbH

EN 60079-0

TUEV14ATEX148929X (II 3 G Ex ec IIC T4 Gc)

CCCEX
CQST/CNEX

CNCA-C23-01

2020312310000213 (Ex ec IIC T4 Gc)

IECEX
TUEV Nord Cert GmbH

IEC 60079-0

IECEX TUN 14.0035 X (Ex ec IIC T4 Gc)

INMETRO
TUV Rheinland do Brasil Ltda.

IEC 60079-0

TUV 12.1297 X

UKEX
WAGO GmbH & Co. KG

EN 60079-0

UKCA_WA GO22UKEX003X_ec

UL
Underwriters Laboratories Inc. (HAZARDOUS LOCATIONS)

UL 121201

E198726

List of Figures

Figure 1	View	6
Figure 2	Indicators	7
Figure 3	CAGE CLAMP® Connections	7
Figure 4	Power Jumper Contacts	8
Figure 5	Schematic Circuit Diagram	9

WAGO GmbH & Co. KG

Postfach 2880 · D - 32385 Minden
Hansastraße 27 · D - 32423 Minden

✉ info@wago.com
🌐 www.wago.com

Headquarters	+49 571/887 – 0
Sales	+49 (0) 571/887 – 44 222
Order Service	+49 (0) 571/887 – 44 333

WAGO is a registered trademark of WAGO Verwaltungsgesellschaft mbH.
Copyright – WAGO GmbH & Co. KG – All rights reserved. The content and structure of the WAGO websites, catalogs, videos and other WAGO media are subject to copyright. Distribution or modification of the contents of these pages and videos is prohibited. Furthermore, the content may neither be copied nor made available to third parties for commercial purposes. Also subject to copyright are the images and videos that were made available to WAGO GmbH & Co. KG by third parties.